

## 3600 PSI Professional

3600 psi - Model 006924-0 (49-State & Canada) UPC: 696471069242  
Model 006924-1 (50-State & Canada) UPC: 696471086683



\*Assembled in the USA using domestic and foreign parts

## FEATURES

### POWERFUL 212cc GENERAC OHV ENGINE

- Larger 0.8 gallon fuel capacity
- Better Lubrication

### Heavy Duty Tri-Plex Pump

- Lasts up to 4 times longer

### Large 10" Pneumatic Wheels

- Easily handle rugged jobsite terrain

### Includes 5 Nozzles

### 30' Flex Hose

- Non-marring
- Abrasion resistant
- Quick connect

### 1 1/4" Steel Frame

- Durable
- Protects components during transport

### 3 Year Limited Warranty

#### PRESSURE AND FLOW

Max Outlet Pressure (psi/bar)	3600/248
Max Flow Rate (gpm)/(L/min)	2.6/9.8

#### ENGINE

Manufacturer	Generac
Displacement (in <sup>3</sup> /cc)	12.9/212
Type	4 cycle/OHV
Orientation	Horizontal
Lubrication Method	Splash
Low Oil Shutdown System	Yes
Fuel Capacity (gal/L)	0.8 / 3
Fuel On/Off Switch	Yes
Oil Capacity (oz/L)	20/0.6
Recommended Engine Oil	10W-30 /SAE 30
Throttle Control	Manual
Choke	Manual
Starting Method	Recoil Pull Start

#### PUMP

Type	Triplex
Material	Aluminum/Brass
Maximum Water Supply Temperature (°F/°C)	100/38

#### HOSE

Type	Polyurethane
Length (ft/m)	30/9.1
Diameter (in/mm)	0.3125/7.9
Rating (psi/bar)	3600/248
Connectors	QC

#### DETERGENT SYSTEM

Chemical Tank	No
Chemical Tank Description	Not Applicable

#### NOZZLES

Nozzle Descriptions	0, 15, 25, 40, Soap
---------------------	---------------------

#### GUN & LANCE

Gun Type	Professional
Gun to Lance Connection	M22
Gun to Hose Connection	QC
Lance Length (in/cm)	29/74
Lance to Nozzle Connection	Quick Change

#### FRAME & MISC.

Handle	Fixed - Click In
Frame Construction	Steel
Wheels (in/cm)	3 x 10/7.6 x 25.4

#### DIMENSIONS & WEIGHTS

Length (in/cm)	40/102
Width (in/cm)	19.2/48.7
Height (in/cm)	24/61
Unit Weight (lbs/kg)	82/37
Boxed Length (in/cm)	24/61
Boxed Width (in/cm)	20.5/52
Boxed Height (in/cm)	20/51
Boxed Weight (lb/kg)	90/40.8

#### WARRANTY

Warranty	3 year limited
----------	----------------