

Electric Start



Model G0088950: (49 State & Canada)
UPC: 696471084528

Model G0088951: (50 State & Canada)
UPC: 696471086676



Included Attachments:



*Built in the USA using domestic and foreign parts

FEATURES

ERGONOMIC SPRAY GUN WITH POWERDIAL™

- Four application settings for optimal cleaning performance—car, wood deck, concrete, soap
- Inverted trigger with cushion grip for extended use

POWERFUL GENERAC OHV ENGINE

- Delivers maximum cleaning performance and reliability
- Longer run time - large 0.8 gallon fuel tank
- Long lasting performance - rated up to 500 hours of use

ELECTRIC START

- One touch push button start
- Long lasting lithium-ion battery will provide up to 50 starts

TIME SAVING ATTACHMENTS

- Power Broom
- Soap Blaster

25' UberFlex™ HOSE

- The most flexible hose in the industry
- Non-kinking
- Non-marring
- Abrasion resistant

Specifications

PRESSURE AND FLOW

Max Outlet Pressure (psi/bar)	3100/214
Max Flow Rate (gpm)/(L/min)	2.5/9.5

ENGINE

Manufacturer	Generac
Displacement (cc)	196
Type	4 cycle/OHV
Orientation	Horizontal
Lubrication Method	Splash
Low Oil Shutdown System	No
Fuel Capacity (qt/L)	3.2/3.0
Fuel On/Off Switch	Yes
Oil Capacity (oz/L)	20/0.6
Recommended Engine Oil	10W-30/SAE 30
Throttle Control	Fixed Speed
Choke	Manual
Starting Method	Electric/Recoil Pull Start

PUMP

Type	Axial Cam
Material	Aluminum
Maximum Water Supply Temperature (°F/°C)	100/38

HOSE

Type	Polyurethane
Length (ft/m)	25/7.6
Diameter (in/mm)	0.25/6.4
Rating (psi/bar)	3400/234
Connectors	M22

DETERGENT SYSTEM

Chemical Tank	Yes
Chemical Tank Size (gal/L)	0.6/2.3

NOZZLES

Nozzle Descriptions	0°, 25°, 40°, Soap, Soap Blaster, Power Broom
---------------------	---

GUN & LANCE

Gun Type	PowerDial™
Gun to Lance Connection	M22
Gun to Hose Connection	M22
Lance Length (in/cm)	20/51
Lance to Nozzle Connection	Quick Change

FRAME & MISC.

Handle	Fixed - Click In
Frame Construction	Steel Welded
Wheels - Never Flat (in/cm)	1.75 x 10/4.4 x 25.4

DIMENSIONS & WEIGHTS

Length (in/cm)	24.4/610
Width (wheel to wheel, in/cm)	19/483
Height (in/cm)	35.5/902
Unit Weight (lbs/kg)	62/28.1
Boxed Length (in/cm)	24/610
Boxed Width (in/cm)	20/508
Boxed Height (in/cm)	22/560
Boxed Weight (lb/kg)	73.2/33.2

WARRANTY

Warranty	3 Year Limited
----------	----------------