

## **Clean Water Pump**

Model G006918-0 (49ST/Canada) UPC: 696471069181 Model G006918-1 (50ST/Canada) UPC: 696471086560

Model G007732-0 (49ST/Canada) UPC: 696471082043 Model G007732-1 (50ST/Canada) UPC: 696471086577





## **FEATURES**

CW20 and

**CW20K** 

- EASY PRIME<sup>™</sup> Funnel design for quick and easy priming
- Powerful Generac Pump Can pump up to 158 gallons per minute
- Color coded suction and discharge ports
  to ensure the correct hose connections
- Durable design Silicon Carbide Seal, Cast Iron Volute and Impeller
- Generac 208cc OHV engine with splash lubrication provides a long engine life

## Specifications

Engine Type	4 cycle/OHV
Engine Displacement (cc)	208
Start Type	Recoil Pull Start
Low Oil Shutdown Method	Low Level
Recommended Oil	10W-30 / SAE30
Fuel Capacity (gal/l)	0.95/3.6
Max Run Time	2.0 hrs
Flow gpm/lpm	158/598
Max Total Head (ft/m)	108/32.9
Max Suction Lift (ft/m)	26/7.9
Mechanical Seal Type	Silicon Carbide
Solid Handling (in)	N/A
Suction Port (NPT)	2.0
Discharge Port (NPT)	2.0
Pump Housing	Aluminum
Impeller	Cast Iron
Volute	Cast Iron

Wheel Kit	N/A
Country of Origin	China
Warranty	1 Year
Manual Part #	0K9077
Length (L) (in/mm)	19.0/482
Width ( <b>W</b> ) (in/mm)	15.8/402
Height ( <b>H</b> ) (in/mm)	17.0/431
Unit Weight (lbs/kg)	53.6/24.3
Carton Length (in/mm)	19.7/499
Carton Width (in/mm)	15.8/402
Carton Height (in/mm)	17.8/453
Shipping Weight (Ibs/kg)	58.4/26.5

Models G007732 Only	
Hose Kit Included	Yes
Discharge Hose Length (ft/m)	25/7.62
Suction Hose Length (ft/m)	12/3.66
Hose Connections	Plastic Speed Nut
Strainer	Plastic



