

Residential Power Washer

GENERAC®

Power Washer



2900 psi - Model 0088740 (50-State & Canada)
UPC: 696471079517



*Assembled in the USA using domestic and foreign parts

FEATURES

POWERFUL GENERAC OHV ENGINE

- Delivers maximum cleaning performance and reliability

AXIAL CAM PUMP WITH EASY-ACCESS HOSE CONNECTIONS

- Prevents kneeling down on the ground

ERGONOMIC SPRAY GUN

- Molded grip, easy-to-pull trigger, and rear hose connection for comfort during prolonged use

NEVER-FLAT TIRES

- Improved mobility on rugged terrain

QUICK CONNECT NOZZLE TIPS

- Easily change the intensity of the spray to suit the application

COMPACT DESIGN

- Minimum storage space required in the garage or shed

2900 psi

specifications

PRESSURE AND FLOW

Max Outlet Pressure (psi/bar)	2900/200
Max Flow Rate (gpm)/(L/min)	2.4/9.0

ENGINE

Manufacturer	Generac
Displacement (in ³ /cc)	11.9/196
Type	4 cycle/OHV
Orientation	Horizontal
Low Oil Shutdown System	No
Fuel Capacity (gal/L)	0.8/3
Fuel On/Off Switch	Yes
Oil Capacity (oz/L)	20/0.6
Recommended Engine Oil	10W-30/SAE 30
Throttle Control	Fixed Speed
Choke	Manual
Starting Method	Recoil Pull Start

PUMP

Type	Axial Cam
Maximum Water Supply Temperature (°F/°C)	100/38

HOSE

Length (ft/m)	25/7.6
Diameter (in/mm)	0.25/6.4
Rating (psi/bar)	3100/214
Connectors	M22 Threaded

NOZZLES

Nozzle Descriptions	0°, 25°, 40°, Soap
---------------------	--------------------

GUN & LANCE

Gun Type	Ergonomic
Gun to Lance Connection	M22 Threaded
Gun to Hose Connection	M22 Threaded
Lance Length (in/cm)	20/51
Lance to Nozzle Connection	Quick Change

FRAME & MISC.

Handle	Fixed - Click In
Frame Construction	Steel
Wheels (in/cm)	1.75/4.4 x 10/25.4 Never Flat

DIMENSIONS & WEIGHTS

Length (in/cm)	24.4/62
Width (wheel to wheel, in/cm)	18.9/47.9
Height (in/cm)	35.5/90.2
Unit Weight (lbs/kg)	57/25.85
Boxed Length (in/cm)	24/61
Boxed Width (in/cm)	20/51
Boxed Height (in/cm)	22/56
Boxed Weight (lb/kg)	72/33

WARRANTY

Warranty	2 Year Limited
----------	----------------