GP5500

GENERAC[®]

GP SERIES Commercial/Residential Portable Generators

Features


- The Generac OHV engine with splash lubrication provides a long engine life.
- Large-capacity steel fuel tank with incorporated fuel gauge provides durability and extended run times.
- Low-oil level shutdown automatically safeguards engine from damage.
- Hardened 1 1/4" steel tube cradle for added durability and strength.
- Fold-down, locking handle for sturdy portability and compact storage.
- Hour Meter tracks maintenance intervals.
- · Heavy-duty, never flat wheels for reliable portability.
- **Covered outlets** provides added protection from the environment and rugged working conditions.

Models 5939-5 / 5939-6 UPC: 696471059397 (49ST)
Model 5975-2 UPC: 696471059755 (49ST/Canada)
Model 5945-1 UPC: 696471059458 (California)



AC Rated Output Running Watts 5500 AC Maximum Output Starting Watts 6875

49-State Control Panel



(2) 120V 20A GFCI 5-20R Duplex Outlets (Model 5945-1)

USA

GP5500

specifications

Product Series	GP5500	
Model (Configuration)	5939-5 / 5939-6 (EPA)	
	5975-2 (EPA/CSA)	
	5945-1 (EPA/CARB)	
AC Rated Output Running Watts:	5500	
AC Maximum Output Motor Starting Watts:	6875	
AC Voltage	120/240 VAC	
AC Frequency	60 Hz	
Rated VAC Amperage	45.8/22.9	
Max Rated VAC Amperage	57.3/28.6	
Engine Displacement	389cc	
Engine Type	OHV	
Engine RPM	3600	
Recommended Oil	10W-30 / SAE30	
Lubrication Method	Splash	
Automatic Voltage Regulation (AVR)	Yes	
Choke Location	On Engine	
Fuel Shut Off	On Fuel Tank	
Starting Method	Recoil Pull Start	
Low Oil Shutdown Method	Low Level	
Neutral Bonded to Ground	Yes	

Start Switch Type	On/Off Switch	
Switch Location	On Engine	
Fuel Gauge	Built-In Tank	
Fuel Tank Capacity Gal (Ltr)	7.2 (27.3)	
Run Time at 50% (Hours)	10	
Handle Style	Single Folding / Locking	
Wheel Type	9.5" Solid Wheels	
Maintenance Kit	Sold Separately	
Warranty - Residential	2 Year Ltd	
Warranty - Commercial	1 Year Ltd	

Dimensions and Weights

	Models 5939-5 / 5939-6	Model 5975-2 Model 5945-1	
Length in (mm)	27.25 (692)		
Width in (mm)	27 (687)		
Height in (mm)	25 (638)		
Extended Length in (mm)	44.5 (1129)		
Carton Length in (mm)	31 (790)		
Carton Width in (mm)	21.5 (550)		
Carton Height in (mm)	23.25 (590)		
Unit Weight lbs (kg)	170.9 (81.3) / 171 (77.5)	170.9 (81.3)	
Shipping Weight lbs (kg)	193 (87.4)		

