

GP2200i

GP SERIESResidential Inverter Portable Generator

Features

- Quiet and Neighbor Friendly fully enclosed design dramatically reduces noise levels.
- TruePowerTM Technology provides clean, stable power ideal for sensitive electronics, tools and appliances.
- Compact and Lightweight makes transportation easy with builtin handle.
- Economy Mode automatically adjusts engine speeds to save fuel and reduce sound emissions.
- Integrated Off/Run/Choke Knob simplifies startup procedures.
- LED Indicators alert you when unit is low on oil, overloaded, or ready-to-use.
- USB Port to charge mobile devices.
- Parallel Ready to connect two GP2200i inverter generators for twice the power. (Parallel kit sold separately.)
- Low-oil Level Shutdown automatically safeguards engine from incurring damage.
- Covered Outlets provide added protection from the environment.

Model 7117-0 UPC: 696471004045 (50-State/CSA)




Model 7118-0 UPC: 696471069303



AC Rated Output Running Watts 1700
AC Maximum Output Starting Watts 2200

Control Panel



GENERAC

Specifications

GP2200i

Product Series	GP2200i
Model (Configuration)	7117-0 (50-State/CSA)
AC Rated Output Running Watts	1700
AC Maximum Output Starting Watts	2200
Rated AC Voltage	120 VAC
Rated AC Frequency	60 Hz
Rated 120 VAC Amperage	14.1
Engine Displacement	80cc
Engine Type	OHV
Engine RPM	Variable
Recommended Oil	10W-30
Oil Capacity Qt (Lts)	0.36 (0.35)
Lubrication Method	Splash
Choke Location	On Control Panel
Fuel Shut Off	On Control Panel
Starting Method	Recoil Pull Start
Low Oil Shutdown	Low Level
Neutral Bonded to Ground	No
Floating Neutral	Yes

Start Switch Type	Off/Run/Choke Knob
Start Switch Location	On Control Panel
Fuel Tank Capacity Gal (Ltrs)	1.2 (4.5)
Run Time at 25% of Rated Load (Hours)	10.75
Warranty- Residential	2 Year Limited
Warranty- Commercial	1 Year Limited

Product Series	GP2200i Parallel Kit (sold separately)
Model	7118-0
Receptacle Type	(1) L5-30R Twist Lock (1) TT-30R (RV)
Rated 120 VAC Amperage	28.2 Amp
AC Rated Voltage	120 V
Warranty- Residential	90 Day Limited
Warranty- Commercial	90 Day Limited

Dimensions and Weights

GP2200i	
Length in (mm)	19.7 (500)
Width in (mm)	11.4 (290)
Height in (mm)	17.9 (454)
Carton Length in (mm)	21.7 (550)
Carton Width in (mm)	12.8 (325)
Carton Height in (mm)	19.3 (490)
Unit Weight lbs (kg)	46.6 (21.14)
Shipping Weight lbs (kg)	53.8 (24.4)

GP2200i Parallel Kit (sold separately)	
Length in (mm)	9.84 (250)
Width in (mm)	4.33 (110)
Height in (mm)	8.27 (210)
Carton Length in (mm)	11.02 (280)
Carton Width in (mm)	9.37 (238)
Carton Height in (mm)	6.10 (155)
Unit Weight lbs (kg)	3.53 (1.6)
Shipping Weight lbs (kg)	3.8 (1.75)



