

3300 WATTS

GP SERIES

Portable Inverter Generator

GENERAC[®]



GP3300i Portable Inverter Generator featuring PowerRush™ Advanced Technology

GP3300i

PORTABLE INVERTER GENERATOR

Light and quiet power on the go.

Power whenever and wherever you need it, the Generac GP3300i inverter featuring new, advanced PowerRush™ technology delivers over 50 percent more starting capacity for your RV essentials and other motor-driven equipment—so you can do more with less.* Quiet inverter power—perfect for outdoor activities in a compact and lightweight solution.

OVER 50% MORE STARTING CAPACITY

with new, advanced PowerRush™ technology so you can do more with less*

QUIET INVERTER POWER

that reduces sound emissions and provides optimal performance

EASY-TO-CARRY

with a compact and lightweight built-in handle

ONE SIMPLE-TO-USE DIAL

that integrates start/run/stop functions with PowerDial™



POWERRUSH™

DOUBLE YOUR POWER

PARALLEL KIT (#7668-0)

A Generac parallel kit allows you to double your power when pairing two inverter generators together with the same output.† Parallel kit sold separately.



*Increases electrical current upon demand; above rated output when starting electric motors.

†Connect any two Generac 3000 or 3500 Series' inverters for twice the power. Applies when pairing two inverter generators with the same output. Parallel kit sold separately.

CONTROL PANEL FEATURES



- **GENERATOR STATUS LIGHTS**
Ready, overload and low oil
- **ECONOMY MODE**
Provides excellent fuel economy and noise reduction
- **USB OUTLETS**
Charge mobile devices including smartphones and tablets
- **PARALLEL READY**
Connect two inverters together for twice the power (parallel kit sold separately)

HOW MUCH POWER DO YOU NEED?

Sizing a portable generator is easy. Check out this example:

- 1** CHOOSE WHICH DEVICES YOU WANT TO POWER AT THE SAME TIME.
- 2** RECORD THE RUNNING WATTS LISTED FOR EACH DEVICE. IF YOUR DEVICE ONLY LISTS AMPS, MULTIPLY THE AMPS BY 120V TO GET WATTAGE. EX. 15A X 120V = 1800 WATTS
- 3** ADD THE RUNNING WATTS TOGETHER FOR ALL DEVICES. THIS IS THE MINIMUM RUNNING WATTAGE REQUIREMENT FOR YOUR NEEDS.

| DEVICE | RUNNING WATTS | GENERATOR SIZE |
|--|---------------|--|
| RV Air Conditioner (13,500 BTU) [†] | 1250 | Minimum running Watts for your needs ↓ 2300 RUNNING WATTS |
| LED/LCD Television | 120 | |
| Blue Ray Player | 15 | |
| Slow Cooker | 250 | |
| Cell Phone Charger | 10 | |
| RV Microwave | 600 | |
| Total | 2245 | |

[†]Motor load, demands higher Watts at start-up.

Watts listed are approximate. Check your appliance for actual requirements. Total wattage requirements assumes intermittent starting of devices.

| | DEVICE | RUNNING WATTS |
|------------|--|---------------|
| RECREATION | RV Air Conditioner (13,500 BTU) [†] | 1250 |
| | Cell Phone Charger | 10 |
| | Box Fan - 20" | 100 |
| | Tablet | 20 |
| | Blue Ray Player | 15 |
| | LED/LCD Television | 120 |
| | Slow Cooker | 250 |
| | Laptop Computer | 75 |
| | Coffee Maker | 900 |
| | RV Microwave | 600 |
| JOBSITE | Blender | 1000 |
| | Hair Dryer | 1500 |
| | Lithium Ion Battery Charger | 360 |
| | Air Compressor [†] | 1000 |
| | Circular Saw [†] | 1400 |
| | Hand Drill [†] | 600 |
| | Belt Sander [†] | 1200 |
| | Reciprocating Saw [†] | 1440 |
| | Table Saw [†] | 1800 |
| | Airless Paint Sprayer | 1080 |
| HOUSEHOLD | Wet Dry Vac | 900 |
| | Quartz Halogen Work Light | 1000 |
| | Refrigerator/Freezer [†] | 700 |
| | Lights | 600 |
| | Desktop Computer | 400 |
| | Sump Pump [†] | 2100 |
| | Toaster | 1200 |
| | Window AC (12,000 BTU) [†] | 3250 |

GP3300i

PORTABLE INVERTER GENERATOR



SPECIFICATIONS

| SERIES | GP3300i |
|-------------------------------------|--|
| Model # | 7154 |
| Configuration | 50ST/CSA |
| Running Watts | 2500 |
| Starting Watts | 3300 |
| Engine Type | Generac OHV |
| Engine Displacement | 149cc |
| Starting Method | Recoil Pull Start |
| Low Oil Shutdown | Yes |
| Fuel Tank Capacity (Gallons) | 1.06 |
| Run Time @ 50% Load | 4.5 hours |
| Run Time @ 25% Load | 7 hours |
| Rated Voltage | 120V |
| Low Total Harmonic Distortion (THD) | Less than 3% |
| Outlets | (2) 120V 20A 5-20R Duplex, (1) 120V 30A L5-30R Twist Lock, (2) USB Outlets |
| Parallel Ready | Yes |
| Handle Style | Single, Molded Into Enclosure |
| Dimensions (L" x W" x H") | 22.3 X 13.4 X 18.4 |
| Product Weight | 59.5 lbs |
| Warranty - Residential | 3 Year Limited |
| Warranty - Commercial | 1 Year Limited |

All portable specifications and models subject to change. Please consult factory for availability.

PARALLEL KIT

| | |
|-------------------------|---|
| Model # (Configuration) | 7668-0 |
| Receptacle Type | (1) 120V 50A 14-50R, (1) 120V 30A TT-30R (RV) |
| Covered Outlets | Yes |
| Rated 120 VAC Amperage | 50 Amp |
| AC Rated Voltage | 120 V |
| Warranty - Residential | 90 Day Limited |
| Warranty - Commercial | 90 Day Limited |
| Dimensions (L x W x H) | 9.84" x 4.33" x 8.27" |

GENERAC®