Mobile Product Portfolio

MLTS / 6

MLT4060

Light Towers – Diesel

Model	Description	kW	Runtime (Hr)	Power Source
MLTS	Narrow Body, Optional 15A Input To Run as Electric	0 - 2.6	166 or 206	Mitsubishi L2E, Kubota Z482
MLT6S	Narrow Body, Export Power	6	164 or 180	Mitsubishi L3E, Kubota D1005
MLT4060	6kW Wide Body, Electric Winch	6	187	Mitsubishi L3E, Kubota D1005
MLT4080	8kW Wide Body, Electric Winch	8	165	Kubota D1105
MLT4150	15kW Wide Body, Electric Winch	15	140	Mitsubishi S4L2
MLT4200	20kW Wide Body, Electric Winch	20	49	Isuzu 4LE2

CTF10

VT Solar

Light Towers – Specialty

Model	Description	Type	Runtime (Hr)	Power Source
CTF10	Run One on Standard Outlet or Two on 20A, 32' Mast	Electric	Unlimited	120V
Cube	60dB(A), Contained & Secure, 300hr Runtime	Diesel	300	Kubota Z482
MLTB	Lithium-Ion Battery System, Cordless, No Noise, No Emissions, Charge in Standard Outlet	Battery	Up to 75	Lithium-Ion Battery
PLT240	Run One on Standard Outlet or Two on 20A, Fits Through Standard Doorway	Electric	Unlimited	120V
VT Solar	3 x 400 W Solar Panels, Solar Charging With Battery	Solar	Unlimited With Sun	Solar

MLG20

MDG175

MDE330

MGG450

Mobile Generators – Gaseous

Model	Description	kW	Fuels	Standard Voltage
MGG210	Trailered, PSI 11.1L Engine	185	NG, LP, Wellhead Gas	480/277 ~ 3
MGG280	Trailered, PSI 14.6L Engine	237	NG, LP, Wellhead Gas	480/277 ~ 3
MGG450	Generac 21.9L Engine	360	NG, LP, Wellhead Gas	480/277 ~ 3

Mobile Generators – Diesel

Model	Description	kW	Engine	Runtime (75%)
MLG8	Trailer Mount, 2" Ball Hitch, Kubota Tier IV	8.1	Kubota 1.13L	79
MLG15	Trailer Mount, 2" Ball Hitch, Mitsubishi Tier IV	13	Mitsubishi 1.8L	41
MLG20	Trailer Mount, 2" Ball Hitch, Isuzu Final Tier IV	19	Isuzu 2.2L	31
MDG25	Skid Mount + Single Axle Trailer	20	Isuzu 2.2L	35
MMG45	Skid Mount + Single Axle Trailer	38	Isuzu 2.2L	36
MDG75	Skid Mount + Single Axle Trailer	60	John Deere 4.5L	42
MDG100	Skid Mount + Single Axle Trailer	80	John Deere 4.5L	29
MDG150	Skid Mount + Single Axle Trailer	120	John Deere 6.8L	48
MDG175	Skid Mount + Single Axle Trailer	140	John Deere 6.8L	40
MDG250	Skid Mount + Single Axle Trailer	200	John Deere 6.8L	30
MDE330	Skid Mount + Dual Axle Trailer	264	Perkins 9.3L	25.2
MDE570	Skid Mount + Triple Axle Trailer	456	Perkins 18.1L	27.1
MDE1140	Triple Axle Air Ride Trailer	912	(2) Perkins 18.1L	27.1
MDE1450	Triple Axle Air Ride Trailer	1,160	(2) Volvo 16.1L	8

MBE30-90

Mobile Battery Energy Storage

Model	Description	kW	Max Capacity (kW h)	Battery Type
MBE30	Skid or Trailered, 30kVA/24kW 208/120V 3-Phase Output, 90kWh Lead Acid, 200A Pass-Through	24	Up to 90	Lead Acid
MBE40	Skid or Trailered, 40kVA/32kW 120/240V 1-Phase Output, 90kWh Lead Acid, 200A Pass-Through	32	Up to 90	Lead Acid

MFH500

MIH800

Industrial Heaters

Model	Description	Type	BTU Output	CFM
MFH500	Non-DEF 74hp Designed for Oil & Gas	Flameless	485,000	5,500
MIH800	1M BTU Self-Contained Job Site Heater	Indirect	805,000	3,900
MIH1.2	Largest Self-Contained Heater in the Industry	Indirect	1,200,000	6,500

CHECK OUT OUR FULL LINE OF MOBILE PRODUCTS HERE →

Check spec sheets for exact specifications.

Generac Power Systems, Inc.
S45W29290 WI-59, Waukesha, WI 53189
Generac.com/Mobile
1-888-Generac (436-3722)

©2025 Generac Power Systems. All rights reserved. Specifications are subject to change without notice.

REV 10/2025

Stationary Generator Product Portfolio

GENERAC® INDUSTRIAL ENERGY

SG080

Small Gensets – Gas

Model	Output (kW)	Controller	Engine	MPS	Fuel Type
SG035	35	G8601	Generac 4.5L	No	NG & LPV
SG040	40	G8601	Generac 4.5L	No	NG & LPV
SG045	45	G8601	Generac 4.5L	No	NG & LPV
SG050NA	50	G8601	Generac 4.5L	No	NG & LPV
SG050TA	50	G8601	Generac 4.5L	No	NG, LPV & LPL
SG060	60	G8601	Generac 4.5L	No	NG, LPV & LPL
SG070	70	G8601	Generac 4.5L	No	NG, LPV & LPL
SG080	80	G8601	Generac 4.5L	No	NG, LPV & LPL
SG080	80	G8601	Generac 8.9L	No	NG, LPV & LPL
SG100	100	G8601	Generac 8.9L	No	NG, LPV & LPL
SG130	130	G8601	Generac 8.9L	Yes	NG, LPV & LPL
SG150	150	G8601	Generac 8.9L	Yes	NG, LPV & LPL

SG450, MG450

Medium Gensets – Gas

Model	Output (kW)	Controller	Engine	MPS
SG150	150	PZ Pro Sync	Generac 14.2L	Yes
SG175	175	PZ Pro Sync	Generac 14.2L	No
SG200	200	PZ Pro Sync	Generac 14.2L	Yes
SG230	230	PZ Pro Sync	Generac 14.2L	No
SG250	250	PZ Pro Sync	Generac 14.2L	Yes
SG275	275	PZ Pro Sync	Generac 14.2L	Yes
SG300	300	PZ Pro Sync	Generac 14.2L	Yes
SG350	350	PZ Pro Sync	Generac 21.9L	Yes
SG400	400	PZ Pro Sync	Generac 21.9L	Yes

SG1000, MG1000

Large Gensets – Gas

Model	Output (kW)	Controller	Engine	MPS
SG500	500	PZ Pro Sync	Generac 25.8L	Yes
SG625	625	PZ Pro Sync	Generac 33.9L	Yes
SG750	750	PZ Pro Sync	Generac 33.9L	Yes
SG1000	1000	PZ Pro Sync	Generac 49L	Yes

CHECK OUT OUR FULL LINE OF INDUSTRIAL GENERATORS HERE →

Check spec sheets for exact specifications.

SD60

Small Gensets – Diesel

Model	Output (kW)	Controller	Engine	MPS
SD10	10	PZ410	Perkins	No
SD15	15	PZ410	Perkins	No
SD20	20	PZ410	Perkins	No
SD25	25	PZ410	Perkins	No
SD30	30	PZ410	Perkins	No
SD35	35	PZ410	Mistubushi	No
SD40	40	PZ410	Mistubushi	No
SD50	50	PZ410	Mistubushi	No
SD60	60	PZ410	FPT	No
SD80	80	PZ410	FPT	No
SD100	100	PZ410	FPT	No
SD130	130	PZ410	FPT	No
SD150	150	G8601	FPT	No
SD175	175	G8601	FPT	No

SD300, MD300

Medium Gensets – Diesel

Model	Output (kW)	Controller	Engine	MPS
SD200	200	H-Panel	FPT	No
SD230	230	H-Panel	FPT	No
SD250	250	H-Panel	FPT	No
SD275	275	H-Panel	FPT	No
SD300	300	H & G-Panel	FPT	Yes
SD350	350	H & G-Panel	FPT	Yes
SD400	400	PZ Pro Sync	Perkins	Yes
SD500	500	PZ Pro Sync	Perkins	Yes
SD600	600	PZ Pro Sync	Perkins	Yes

SD2500

Large Gensets – Diesel

Model	Output (kW)	Controller	Engine	MPS
SD750	750	PZ Pro Sync	Perkins	Yes
SD750	750	Inteligen	MHI	Yes
SD800	800	Inteligen	MHI	Yes
SD900	900	PZ Pro Sync	Perkins	Yes
SD1000	1000	PZ Pro Sync	Perkins	Yes
SD1250	1250	Inteligen	MHI	Yes
SD1500	1500	Inteligen	MHI	Yes
SD2000	2000	Inteligen	MHI	Yes
SD2250	2250	G8601	Baudouin	Yes
SD2500	2500	G8601	Baudouin	Yes
SD2750	2750	G8601	Baudouin	Yes
SD3000	3000	G8601	Baudouin	Yes
SD3250	3250	G8601	Baudouin	Yes