

10-22kW GUARDIAN® SERIES

GENERAC®

Home Standby Generators



WITH FREE
**MOBILE LINK WIRELESS
CONNECTIVITY**

Choose the #1 selling home standby generator brand

Generac's Guardian Series generators provide the automatic backup power you need to protect your home and family during a power outage. Connected to your existing LP or natural gas fuel supply, it kicks in within seconds of sensing power loss—automatically—and runs for as long as necessary until utility power returns. Choose from Generac's industry leading lineup to power just the essentials or Generac's 22kW, the largest air-cooled generator in the market, for whole-house coverage.

Features & Benefits:



GENERAC'S G-FORCE ENGINE

Are purpose-built, pressure-lubricated engines capable of handling the rigors of generator use, resulting in power that's more reliable and requires less routine maintenance than any competitive engine. Generac's G-Force engine features hydraulic lifters—improving engine performance and extending the life of the product. (Hydraulic lifters only available on the 13 & 16 kW)



TRUEPOWER™ TECHNOLOGY

Delivers best-in-class power quality with less than 5% total harmonic distortion for clean, smooth operation of sensitive electronics and appliances.



QUIET-TEST™ SELF-TEST MODE

Runs at a lower RPM for a five or twelve minute test, making generators significantly quieter than other brands, while consuming less fuel.



GENERAC'S EVOLUTION™ CONTROLLER

Features a multilingual LCD display that allows you to monitor battery status and track maintenance intervals to ensure your generator is always in top operating condition.




TOUGH, DURABLE ENCLOSURES

Our RhinoCoat™ powder-coated finish helps make corrosion-resistant aluminum perfect for all weather conditions.



Mobile Link™



Available for FREE with every Guardian Series home standby generator, Mobile Link allows you to monitor the status of your generator from anywhere in the world using a smart phone, tablet, or PC. Easily access information, such as the current operating status and maintenance alerts. With Mobile Link, you are taken care of before the next power outage.

Also Featuring:



24/7/365 CUSTOMER SUPPORT TEAM

Standing by all day, every day from our headquarters in Wisconsin to answer any questions you might have.



BUILT IN THE USA*

Generac generators and engines are engineered and built in the USA*

**Assembled in the USA using domestic and foreign parts.*



5-YEAR LIMITED WARRANTY

Included with all home standby generators.



Home Standby Generators

SPECIFICATIONS (LP/NG)	10/9 kW	13/13 kW	16/16 kW	20/18 kW		22/19.5 kW	
Generator Only Model	7171	7173	7176	7038		7042	
Generator / 100 Amp Select Circuit Switch Model	7172	7174	7177	-		-	
Generator / 200 Amp Service Rated Load Shedding Smart Switch Package Model	-	7175	7178	7039		7043	
Voltage (Single Phase)	120 / 240						
Amps @ 240V LPG	41.7	54.2	66.6	83.3		91.7	
Amps @ 240V NG	37.5	54.2	66.6	75		81.3	
Engine/Alternator RPM	3600 / 3600						
Engine	Generac G-Force						
Engine Displacement	460cc	816cc		999cc			
Fuel Consumption @ 1/2 Load - NG cu. ft/hr	101	154	182	204*	164	228**	203
Fuel Consumption @ Full Load - NG cu. ft/hr	127	225	245	301*	287	327**	306
Fuel Consumption @ 1/2 Load - LPG cu. ft/hr	36 (0.97)	56 (1.54)	62 (1.70)	86 (2.37)*	86 (2.36)	92 (2.53)**	92 (2.53)
Fuel Consumption @ Full Load - LPG cu. ft/hr	54 (1.48)	90 (2.45)	109 (2.99)	129.6 (3.56)*	136 (3.74)	142.1 (3.90)**	142.1 (3.90)
Quiet-Test Mode	Yes						
db(A) at Exercise	57	55		57		57	
db(A) at Normal Operating Load	61	65		67			
Enclosure	Aluminum						
Enclosure Color	Bisque						
Warranty	5-Year Limited						
Dimensions - L" x W" x H" in. (mm)	48 x 25 x 29 (1218 x 638 x 727)						
Weight (lb)	338	385	420	448*	436	466**	445
Mobile Link Wireless Connectivity	Yes						

*7038-1 & 7039-1 specifications

**7042-2 & 7043-2 specifications



NATIONWIDE DEALER SERVICE NETWORK

Generac's commitment to service includes scheduled maintenance programs, warranty assistance and emergency service to ensure that Generac customers are never left powerless. The largest nationwide dealer network has factory-trained technicians on staff and maintains large inventories of Generac parts, components and accessories. Find a dealer near you at Generac.com.

Generac Power Systems, Inc.
S45 W29290 Hwy. 59, Waukesha, WI 53189

www.Generac.com | 888-GENERAC (436-3722)

0203010 REV 05/20

©2020 Generac Power Systems. All rights reserved.
Specifications are subject to change without notice.

GENERAC®