

# ***PRODUCT INFORMATION BULLETIN***

**DATE:** August 2022 (Rev A)

**SUBJECT:** Air Cooled Home Standby High Altitude Kits

**MODELS AFFECTED:** All air cooled home standby units.

**WARRANTY:** Information only.

**CONCERN:** Generac high altitude kits are available, which can be used on new or existing air cooled home standby generators installed in elevations over 2,000 ft (610 m) above sea level.

**CORRECTIVE ACTION:** A high altitude kit may be required when operating over 2,000 ft (610 m) above sea level per U.S EPA regulations. Operating the engine with the incorrect engine configuration at a given altitude may increase emissions and decrease fuel efficiency and performance.

High altitude kit fitment applications are listed below.

| Model No. | Description                    | Node  | Kit Family Table PN | High Altitude Kit Model Number |
|-----------|--------------------------------|-------|---------------------|--------------------------------|
| G0071640  | 11KW/530 DR-NO T/SW AL         | 11 kW | 0J4930A             | G0072950                       |
| G0070671  | 11KW/530 EATON-NO T/SW AL      | 11 kW | 0J4930A             | G0072950                       |
| G0070331  | 11KW/530 GRD+200A SE T/SW AL   | 11 kW | 0J4930A             | G0072950                       |
| G0070321  | 11KW/530 GUARD+16C T/SW AL     | 11 kW | 0J4930A             | G0072950                       |
| G0070311  | 11KW/530 GUARD-NO T/SW AL      | 11 kW | 0J4930A             | G0072950                       |
| G0071400  | 11KW/530 HNYWL+16C T/S AL      | 11 kW | 0J4930A             | G0072950                       |
| G0070581  | 11KW/530 HNYWL-NO T/SW AL      | 11 kW | 0J4930A             | G0072950                       |
| G0070721  | 11KW/530 SIEMENS-NO T/SW AL    | 11 kW | 0J4930A             | G0072950                       |
| G0071650  | 20KW/999 DR-NO T/SW AL         | 20 kW | 0L5581              | G0073030                       |
| G0070691  | 20KW/999 EATON-NO T/SW AL      | 20 kW | 0L5581              | G0073030                       |
| G0070391  | 20KW/999 GRD+200A SE T/SW AL   | 20 kW | 0L5581              | G0073030                       |
| G0070381  | 20KW/999 GUARD-NO T/SW AL      | 20 kW | 0L5581              | G0073030                       |
| G0070642  | 20KW/999 HNYWL +200A SE T/S AL | 20 kW | 0L5581              | G0073030                       |
| G0070632  | 20KW/999 HNYWL +200A SE T/S AL | 20 kW | 0L5581              | G0073030                       |
| G0070621  | 20KW/999 HNYWL-NO T/SW AL      | 20 kW | 0L5581              | G0073030                       |
| G0070741  | 20KW/999 SIEMENS-NO T/SW AL    | 20 kW | 0L5581              | G0073030                       |
| G0071630  | 15KW/999 ECOGEN-NO T/SW AL     | 15 kW | 0L5581              | G0073050                       |
| G0070661  | 9KW/426 EATON-NO T/SW AL       | 9 kW  | 0K3661              | G0072980                       |
| G0070301  | 9KW/426 GUARD+ 16C T/SW AL     | 9 kW  | 0K3661              | G0072980                       |
| G0070291  | 9KW/426 GUARD-NO T/SW AL       | 9 kW  | 0K3661              | G0072980                       |
| G0070571  | 9KW/426 HNYWL-NO T/SW AL       | 9 kW  | 0K3661              | G0072980                       |

Confidential information subject to Article IV of the Domestic Non-Exclusive Buy/Sell Agreement. Do not disclose.

**GENERAC**<sup>®</sup>

| Model No. | Description                              | Node  | Kit Family Table PN | High Altitude Kit Model Number |
|-----------|------------------------------------------|-------|---------------------|--------------------------------|
| G0070711  | 9KW/426 SIEMENS-NO T/SW AL               | 9 kW  | 0K3661              | G0072980                       |
| G0070681  | 16KW/999 EATON-NO T/SW AL                | 16 kW | 0L5581              | G0073020                       |
| G0070371  | 16KW/999 GRD+200A SE T/SW AL             | 16 kW | 0L5581              | G0073020                       |
| G0070361  | 16KW/999 GUARD+16C T/SW AL               | 16 kW | 0L5581              | G0073020                       |
| G0070351  | 16KW/999 GUARD-NO T/SW AL                | 16 kW | 0L5581              | G0073020                       |
| G0070591  | 16KW/999 HNYWL-NO T/SW AL                | 16 kW | 0L5581              | G0073020                       |
| G0070731  | 16KW/999 SIEMENS-NO T/SW AL              | 16 kW | 0L5581              | G0073020                       |
| G0071410  | 16KW/999 RESPONSE+ 200A SE T/S AL        | 16 kW | 0L5581              | G0073050                       |
| G0071411  | 16KW/999 RESPONSE+ 200A SE T/S AL        | 16 kW | 0L5581              | G0073050                       |
| G0070393  | 20KW/999 GRD+200A SE T/SW AL             | 20 kW | 0L5581              | G0073030                       |
| G0070383  | 20KW/999 GUARD-NO T/SW AL                | 20 kW | 0L5581              | G0073030                       |
| G0070643  | 20KW/999 HNYWL +200A CUL AL              | 20 kW | 0L5581              | G0073030                       |
| G0070633  | 20KW/999 HNYWL +200A SE T/S AL           | 20 kW | 0L5581              | G0073030                       |
| G0070623  | 20KW/999 HNYWL-NO T/SW AL                | 20 kW | 0L5581              | G0073030                       |
| G0072101  | 24KW/999 GUARD+200A SE T/SW AL           | 24 kW | 0L5581              | G0073060                       |
| G0072370  | 24KW/999 GUARD+200A SE T/SW AL           | 24 kW | 0L5581              | G0073060                       |
| G0072100  | 24KW/999 GUARD+200A SE T/SW AL           | 24 kW | 0L5581              | G0073060                       |
| G0072109  | 24KW/999 GUARD+200A SE T/SW WI-FI CAP AL | 24 kW | 0L5581              | G0073060                       |
| G0072090  | 24KW/999 GUARD-NO T/SW AL                | 24 kW | 0L5581              | G0073060                       |
| G0072099  | 24KW/999 GUARD-NO T/SW WI-FI CAP AL      | 24 kW | 0L5581              | G0073060                       |
| G0072130  | 24KW/999 HNYW-NO T/SW AL                 | 24 kW | 0L5581              | G0073060                       |
| G0072139  | 24KW/999 HNYW-NO T/SW WI-FI CAP AL       | 24 kW | 0L5581              | G0073060                       |
| G0062510  | 8KW/410 CENT +10C T/SW STL               | 8 kW  | 0K3661              | G0072970                       |
| G0062720  | 8KW/410 EATON NO T/SW STL                | 8 kW  | 0K3661              | G0072970                       |
| G0062450  | 8KW/410 GRD/GENANO T/SW STL              | 8 kW  | 0K3661              | G0072970                       |
| G0062370  | 8KW/410 GUARD+ 10C T/SW                  | 8 kW  | 0K3661              | G0072970                       |
| G0067030  | 8KW/410 HNYWL NO T/SW AL                 | 8 kW  | 0K3661              | G0072970                       |
| G0062630  | 8KW/410 SMNSANO T/SW STL                 | 8 kW  | 0K3661              | G0072970                       |
| G0062810  | 15KW/990 CENT +200A SE T/S STL           | 15 kW | A0002789944         | G0072940                       |
| G0062610  | 15KW/990 HNYWL NO T/SW AL                | 15 kW | A0002789944         | G0072940                       |
| G0062561  | 16KW/990 CENT +16C T/SW STL              | 16 kW | A0002789944         | G0072940                       |

Confidential information subject to Article IV of the Domestic Non-Exclusive Buy/Sell Agreement. Do not disclose.



| Model No. | Description                    | Node  | Kit Family<br>Table PN | High Altitude Kit<br>Model Number |
|-----------|--------------------------------|-------|------------------------|-----------------------------------|
| G0062560  | 16KW/990 CENT +16C T/SW STL    | 16 kW | A0002789944            | G0072940                          |
| G0062572  | 16KW/990 CENT +200A SE T/S STL | 16 kW | A0002789944            | G0072940                          |
| G0062573  | 16KW/990 CENT +200A SE T/S STL | 16 kW | A0002789944            | G0072940                          |
| G0062570  | 16KW/990 CNT +200A SE T/S AL   | 16 kW | A0002789944            | G0072940                          |
| G0062571  | 16KW/990 CNT +200A SE T/S STL  | 16 kW | A0002789944            | G0072940                          |
| G0067231  | 16KW/990 EATON NO T/SW AL      | 16 kW | A0002789944            | G0072940                          |
| G0067230  | 16KW/990 EATON NO T/SW STL     | 16 kW | A0002789944            | G0072940                          |
| G0067011  | 16KW/990 EATON NO T/SW STL     | 16 kW | A0002789944            | G0072940                          |
| G0067010  | 16KW/990 EATON NO T/SW STL     | 16 kW | A0002789944            | G0072940                          |
| G0064592  | 16KW/990 GRD/GENANO T/SW STL   | 16 kW | A0002789944            | G0072940                          |
| G0064591  | 16KW/990 GRD/GENANO T/SW STL   | 16 kW | A0002789944            | G0072940                          |
| G0067210  | 16KW/990 GRD/GEN NO T/SW AL    | 16 kW | A0002789944            | G0072940                          |
| G0067211  | 16KW/990 GRD/GEN NO T/SW AL    | 16 kW | A0002789944            | G0072940                          |
| G0064620  | 16KW/990 GRD +200A SE T/SW STL | 16 kW | A0002789944            | G0072940                          |
| G0064621  | 16KW/990 GRD +200A SE T/SW STL | 16 kW | A0002789944            | G0072940                          |
| G0064622  | 16KW/990 GRD +200A SE T/SW STL | 16 kW | A0002789944            | G0072940                          |
| G0064610  | 16KW/990 GUARD+ 16C T/SW STL   | 16 kW | A0002789944            | G0072940                          |
| G0064611  | 16KW/990 GUARD+ 16C T/SW STL   | 16 kW | A0002789944            | G0072940                          |
| G0067021  | 16KW/990 HONEYWELL NO T/SW AL  | 16 kW | A0002789944            | G0072940                          |
| G0067020  | 16KW/990 HONEYWELL NO T/SW AL  | 16 kW | A0002789944            | G0072940                          |
| G0067250  | 16KW/990 SIEMENS NO T/SW AL    | 16 kW | A0002789944            | G0072940                          |
| G0067251  | 16KW/990 SIEMENS NO T/SW AL    | 16 kW | A0002789944            | G0072940                          |
| G0067000  | 16KW/990 SMNS NO T/SW STL      | 16 kW | A0002789944            | G0072940                          |
| G0067001  | 16KW/990 SMNS NO T/SW STL      | 16 kW | A0002789944            | G0072940                          |
| G0062760  | 17KW/990 EATON NO T/SW AL      | 17 kW | A0002789944            | G0072940                          |
| G0062750  | 17KW/990 EATON NO T/SW STL     | 17 kW | A0002789944            | G0072940                          |
| G0062490  | 17KW/990 GRD/GENANO T/S AL     | 17 kW | A0002789944            | G0072940                          |
| G0062480  | 17KW/990 GRD/GENANO T/SW       | 17 kW | A0002789944            | G0072940                          |
| G0062430  | 17KW/990 GRD+200A SE T/SW      | 17 kW | A0002789944            | G0072940                          |
| G0062420  | 17KW/990 GUARD+ 16C T/SW       | 17 kW | A0002789944            | G0072940                          |
| G0062600  | 17KW/990 HNYWL +200A SE        | 17 kW | A0002789944            | G0072940                          |

Confidential information subject to Article IV of the Domestic Non-Exclusive Buy/Sell Agreement. Do not disclose.

**GENERAC®**

| Model No. | Description                      | Node  | Kit Family<br>Table PN | High Altitude Kit<br>Model Number |
|-----------|----------------------------------|-------|------------------------|-----------------------------------|
| G0062601  | 17KW/990 HNYWL +200A SE          | 17 kW | A0002789944            | G0072940                          |
| G0062602  | 17KW/990 HNYWL +200A SE STL      | 17 kW | A0002789944            | G0072940                          |
| G0062820  | 17KW/990 HNYWL +200 CS T/S STL   | 17 kW | A0002789944            | G0072940                          |
| G0062821  | 17KW/990 HNYWL +200 CSA T/S STL  | 17 kW | A0002789944            | G0072940                          |
| G0062670  | 17KW/990 SMNSANO T/SW AL         | 17 kW | A0002789944            | G0072940                          |
| G0062660  | 17KW/990 SMNSANO T/SW STL        | 17 kW | A0002789944            | G0072940                          |
| G0070350  | 16KW/999 GUARD-NO T/SW AL        | 16 kW | 0L5581                 | G0073020                          |
| G0070360  | 16KW/999 GUARD+ 16C T/SW AL      | 16 kW | 0L5581                 | G0073020                          |
| G0070370  | 16KW/999 GRD+ 200A SE T/SW AL    | 16 kW | 0L5581                 | G0073020                          |
| G0070380  | 20KW/999 GUARD-NO T/SW AL        | 20 kW | 0L5581                 | G0073030                          |
| G0070390  | 20KW/999 GRD+ 200A SE T/SW AL    | 20 kW | 0L5581                 | G0073030                          |
| G0070590  | 16KW/999 HNYWL-NO T/SW AL        | 16 kW | 0L5581                 | G0073020                          |
| G0070600  | 17KW/999 HNYWL +200A SE T/S STL  | 17 kW | 0L5581                 | G0073020                          |
| G0070610  | 17KW/999 HNYWL +200A CSA T/S STL | 17 kW | 0L5581                 | G0073020                          |
| G0070620  | 20KW/999 HNYWL-NO T/SW AL        | 20 kW | 0L5581                 | G0073030                          |
| G0070630  | 20KW/999 HNYWL +200A SE T/S STL  | 20 kW | 0L5581                 | G0073030                          |
| G0070631  | 20KW/999 HNYWL +200A SE T/S STL  | 20 kW | 0L5581                 | G0073030                          |
| G0070640  | 20KW/999 HNYWL +200A CSA STL     | 20 kW | 0L5581                 | G0073030                          |
| G0070641  | 20KW/999 HNYWL +200A CSA STL     | 20 kW | 0L5581                 | G0073030                          |
| G0070680  | 16KW/999 EATON-NO T/SW AL        | 16 kW | 0L5581                 | G0073020                          |
| G0070690  | 20KW/999 EATON-NO T/SW AL        | 20 kW | 0L5581                 | G0073030                          |
| G0070730  | 16KW/999 SIEMENS-NO T/SW AL      | 16 kW | 0L5581                 | G0073020                          |
| G0070740  | 20KW/999 SIEMENS-NO T/SW AL      | 20 kW | 0L5581                 | G0073030                          |
| G0070700  | 22KW/999 EATON-NO T/SW AL        | 22 kW | 0L5581                 | G0073040                          |
| G0070430  | 22KW/999 GUARD +200A SE T/SW AL  | 22 kW | 0L5581                 | G0073040                          |
| G0070420  | 22KW/999 GUARD-NO T/SW AL        | 22 kW | 0L5581                 | G0073040                          |
| G0070650  | 22KW/999 HNYW-NO T/SW AL         | 22 kW | 0L5581                 | G0073040                          |
| G0070750  | 22KW/999 SIEMENS-NO T/SW AL      | 22 kW | 0L5581                 | G0073040                          |
| G0061030  | 15KW/999 ECOGEN                  | 15 kW | A0002789944            | G0072940                          |
| G0070670  | 11KW/530 EATON-NO T/SW AL        | 11 kW | 0J4930A                | G0072950                          |
| G0070330  | 11KW/530 GRD+200A SE T/SW AL     | 11 kW | 0J4930A                | G0072950                          |

Confidential information subject to Article IV of the Domestic Non-Exclusive Buy/Sell Agreement. Do not disclose.

**GENERAC®**

| Model No. | Description                                 | Node  | Kit Family<br>Table PN | High Altitude Kit<br>Model Number |
|-----------|---------------------------------------------|-------|------------------------|-----------------------------------|
| G0070320  | 11KW/530 GUARD+ 16C T/SW AL                 | 11 kW | 0J4930A                | G0072950                          |
| G0070310  | 11KW/530 GUARD-NO T/SW AL                   | 11 kW | 0J4930A                | G0072950                          |
| G0070580  | 11KW/530 HNYWL-NO T/SW AL                   | 11 kW | 0J4930A                | G0072950                          |
| G0070720  | 11KW/530 SIEMENS-NO T/SW AL                 | 11 kW | 0J4930A                | G0072950                          |
| G0070660  | 9KW/426 EATON-NO T/SW AL                    | 9 kW  | 0K3661                 | G0072980                          |
| G0070300  | 9KW/426 GUARD+ 16C T/SW AL                  | 9 kW  | 0K3661                 | G0072980                          |
| G0070290  | 9KW/426 GUARD-NO T/SW AL                    | 9 kW  | 0K3661                 | G0072980                          |
| G0070570  | 9KW/426 HNYWL-NO T/SW AL                    | 9 kW  | 0K3661                 | G0072980                          |
| G0070710  | 9KW/426 SIEMENS-NO T/SW AL                  | 9 kW  | 0K3661                 | G0072980                          |
| G0072910  | 26KW/999 GUARD+200A SE T/SW AL              | 26 kW | 0L5581                 | G0073010                          |
| G0072919  | 26KW/999 GUARD+200A SE T/SW WI-FI<br>CAP AL | 26 kW | 0L5581                 | G0073010                          |
| G0072900  | 26KW/999 GUARD-NO T/SW AL                   | 26 kW | 0L5581                 | G0073010                          |
| G0072909  | 26KW/999 GUARD-NO T/SW WI-FI CAP AL         | 26 kW | 0L5581                 | G0073010                          |
| G0072920  | 26KW/999 HNYW-NO T/SW AL                    | 26 kW | 0L5581                 | G0073010                          |
| G0072929  | 26KW/999 HNYW-NO T/SW WI-FI CAP AL          | 26 kW | 0L5581                 | G0073010                          |