



# GROUP EV



# GROUP EV



EV GENERATOR 426 ES  
PORT XC CARB

**EXPLODED VIEW: EV GENERATOR 426 ES PORT XC CARB**

**DRAWING #: 1000005844**

**GROUP EV**

ITEM	PART#	QTY.	DESCRIPTION
------	-------	------	-------------

PAGE 1

1	10000008370	1	MUFFLER GTH530 W/SA
2	0G3730B	2	SCREW SHC M8-1.25 X 25 G8.8 SEMS
3	0C4138	1	GASKET EXHAUST PORT
4	0L5637	1	MANIFOLD EXHAUST 426CC PORT
5	0L2391	1	GASKET EXHAUST 426
6	0L3117	1	ENGINE GH426 PORT XP CARB
7	10000007873	1	ALT 8000W COPPER BRUSH TYPE
8	10000000245	1	BRACKET MUFFLER XC
9	10000003425	1	DECAL FUEL OVERFLOW PRO SERIES
10	0L5761	1	DECAL DATA PLATE FUEL TANK XP
11	0L5761A	1	DECAL BLANK PLATE FUEL TANK XP
12	0H0116B	1	DECAL WARN HOT EXHAUST
13	0H4635B	1	DECAL DANGER &#38; SAFETY RUS
14	0H9004	1	DECAL LIFT WARNING XP PORT
15	0G5445	4	SCREW HHTT M8-1.25 X 20
16	0H8250	1	DECAL CO WARNING 3L PRODC T HOR
17	0L0207	1	FUEL TNK 9 GAL ASSY
18	067989	13	NUT HEX FL WHIZ M8-1.25
19	0H7520	1	FUEL GAUGE,ROUND 6 LONG
20	0H7521	1	GROMMET FUEL GAUGE ROUND
21	0H2043	2	VIB MOUNT 35 X 12 X M8-1.25
22	10000003289	1	ST03 BRACKET ENGINE MOUNT XP
23	081990	4	SCREW SHC M8-1.25 X 40 C8.8
24	084508A	2	VIBRATION MNT 45 ANGLE 65 DURO
25	0H0919	1	ASSEMBLY,BRUSH VISION
26	G051713	4	WASHER FLAT M5
27	G049815	4	SCREW HHC M5-0.8 X 16 G8.8
28	0H2579D	1	AVR TT816-100
29	0H3049	1	COVER ALTERNATOR INLET 5-7KW
30	G052618	2	SCREW HHC M5-0.8 X 12 C8.8
31	G049226	2	WASHER LOCK M5
32	G046526	4	WASHER LOCK M10
33	G022511	4	SCREW HHC 3/8-16 X 1-1/4 G5
34	0H1411B	4	RUBBER MOUNT 10.3 ID X 11 HGT
35	0H1610A	4	ANTI-CRUSH 10.80D 9ID 10LG
36	0H0958A	1	ASSY GAS CAP SEALED - BLACK
37	0H1326	1	FILTER FUEL
38	10000004136	1	SPARK ARRESTOR
39	10000000680	1	VALVE FUEL SHUTOFF PRO SERIES
40	10000000650	1	KNOB FUEL VALVE TOUCH POINT PRO
41	0K9238	1	SCREW BFHSC M3-0.5 X 16 BLK ZP
42	0H5994	1	CARBON CANISTER,407CC ENGINE
43	0H5993	1	BRACKET,CARBON CAN 407CC ENGINE
44	10000001888	1	ST0R BRACKET CARBON CAN PRO
45	0L2176	2	SCREW HHSD PREMIUM 1/4-14X1 BZ
46	0H1207C	1	HOSE 11MM ODX 5.5MM IDX 16.5IN
47	043146	2	SCREW HHC M6-1.0 X 10 C8.8
48	0E8388	2	NUT HEX FL WHIZ M6-1.0
49	10000000743	6	SCREW HHFCS M8-1.25 X 25 C8.8

PAGE 2

1	10000003248	2	ST15 LIFTING EYE XC
2	10000003291	2	ST03 LIFT EYE COVER XC
3	10000000188	2	BINDING POST ASSEMBLY #10-24 TH
4	0J9125	6	NUT HEX FL WHIZ M8-1.25
5	0G5445	2	SCREW HHTT M8-1.25 X 20
6	0K9233	12	SCREW HHFCS M6-1.0 X 20 G8.8
7	0J1321	12	WASHER FLAT M6 NYLON
8	10000003233	1	ST19 SKIRT LONG SIDE XP
9	10000001958	5	NUT CLIP-ON M6X1.0
10	0G6392	1	BOOT VINYL STARTER-SOLENOID
11	075763A	1	BOOT BATTERY CABLE
12	0742600196	1	WIRE ASSY SOL TO BATT-POS

**EXPLODED VIEW: EV GENERATOR 426 ES PORT XC CARB****DRAWING #: 1000005844****GROUP EV**

<b>ITEM</b>	<b>PART#</b>	<b>QTY.</b>	<b>DESCRIPTION</b>
13	052618	4	SCREW HHC M5-0.8 X 12 C8.8
14	0H3535	6	NUT FLANGE M5-0.8 NYLOCK
15	0742600193	1	WIRE ASSEMBLY
16	0H7945	1	ASSEMBLY BATTERY STRAP
17	10000003250	1	ST19 SKIRT ALTERNATOR SIDE XC
18	0H1779	8	SCREW HHFC M8-1.25 X 45
19	10000007075	1	ST03 FRAME ONE-PIECE XC6500E/8000E
20	10000003285	1	ST03 BRACKET HANDLE
21	0H1782	2	CAP NUT M8-1.25 BLACK ZINC
22	0L5584	1	SPRING PLUNGER M16 X 2
23	10000003284	1	ST03 BRACKET HANDLE
24	10000000732	2	SPACER SHOULDER 5/16 ID NYLON
25	10000000187	2	BOLT SHOULDER LOW PROFILE M6X1.0
26	0G3110	1	SCREW HHTT M6-1.0 X 20 ZINC
27	0A1658	1	WASHER LOCK SPECIAL 1/4"
28	0742600194	1	GRND WIRE PORT BRG CARR-FRAME
29	055414	1	LUG SLDLSS #2-#8 X 17/64 CU
30	067210B	1	DECAL GROUND
31	097400	1	CSA HIPOT DECAL
32	10000000568	1	ASSY C-PNL XC8000E
33	10000003245	1	ST19 SKIRT CONTROL PANEL SIDE XC
34	0K3130	6	SCREW PPPH M5-0.8 X 16 BZC
35	10000004210	1	DECAL BRAND C-PNL XC8000E
36	0K8672	1	AXLE 15.87 DIA X 684 CLR ZINC
37	10000003228	2	WHEEL 10" DIA SKID PATTERN
38	022247	2	WASHER FLAT 5/8 ZINC
39	0H3443	2	COTTER HAIRPIN 2.56 X .80
40	10000010375	2	FOOT ASSEMBLY XC
41	0E8388	1	NUT HEX FL WHIZ M6-1.0
42	0A1718	1	SCREW SET M8-1.25 X 8
43	10000002475	1	DECAL QUICK START PRO SERIES
44	10000003454	1	ST19 SKIRT ENGINE SIDE XC
45	0L57660AL15	1	LATCH HANDLE XC ORANGE
46	10000007045	1	ST03 WELD HDL H-STYLE FOLD DOWN XC
47	10000003055	2	HANDLE GRIP PRO SERIES
48	0H1780B	2	CURVED HEAD M8-1.25 X 50MM LNG
49	0G9449	1	BATTERY 12V SEALED