


SD080

Liquid Cooled Diesel Engine Generator Sets

Standby Power Rating
80KW 60 Hz / 80KVA 50 Hz

Prime Power Rating
64KW 60 Hz /64KVA 50 Hz



Power Matched
GENERAC 3.9DTA ENGINE
Turbocharged/Aftercooled

FEATURES

- **INNOVATIVE DESIGN & PROTOTYPE TESTING** are key components of GENERAC'S success in "IMPROVING POWER BY DESIGN." But it doesn't stop there. Total commitment to component testing, reliability testing, environmental testing, destruction and life testing, plus testing to applicable CSA, NEMA, EGSA, and other standards, allows you to choose GENERAC POWER SYSTEMS with the confidence that these systems will provide superior performance.
- **TEST CRITERIA:**
 - ✓ PROTOTYPE TESTED
 - ✓ SYSTEM TORSIONAL TESTED
 - ✓ ELECTRO-MAGNETIC INTERFERENCE
 - ✓ NEMA MG1 EVALUATION
 - ✓ MOTOR STARTING ABILITY
 - ✓ SHORT CIRCUIT TESTING
 - ✓ UL 2200 COMPLIANCE AVAILABLE
- **SOLID-STATE, FREQUENCY COMPENSATED VOLTAGE REGULATION.** This state-of-the-art power maximizing regulation system is standard on all Generac models. It provides optimized FAST RESPONSE to changing load conditions and MAXIMUM MOTOR STARTING CAPABILITY by electronically torque-matching the surge loads to the engine.
- **SINGLE SOURCE SERVICE RESPONSE** from Generac's dealer network provides parts and service know-how for the entire unit, from the engine to the smallest electronic component. You are never on your own when you own a GENERAC POWER SYSTEM.
- **ECONOMICAL DIESEL POWER.** Low cost operation due to modern diesel engine technology. Better fuel utilization plus lower cost per gallon provide real savings.
- **LONGER ENGINE LIFE.** Generac heavy-duty diesels provide long and reliable operating life.
- **GENERAC TRANSFER SWITCHES, SWITCHGEAR AND ACCESSORIES.** Long life and reliability is synonymous with GENERAC POWER SYSTEMS. One reason for this confidence is that the GENERAC product line includes its own transfer systems, accessories, switchgear and controls for total system compatibility.

GENERAC[®]
POWER SYSTEMS, INC.

GENERATOR SPECIFICATIONS

TYPE	Four-pole, revolving field
ROTOR INSULATION	Class H
STATOR INSULATION	Class H
TOTAL HARMONIC DISTORTION	<3%
TELEPHONE INTERFERENCE FACTOR (TIF)	<50
ALTERNATOR	Self-ventilated and drip-proof
BEARINGS (PRE-LUBED & SEALED)	1
COUPLING	Direct, Flexible Disc
LOAD CAPACITY (STANDBY)	100%
LOAD CAPACITY (PRIME)	110%

NOTE: Emergency loading in compliance with NFPA 99, NFPA 110. Generator rating and performance in accordance with ISO8528-5, BS5514, SAE J1349, ISO3046 and DIN6271 standards.

EXCITATION SYSTEM

- BRUSHLESS..... Magnetically coupled DC current ✓
 - Eight-pole exciter w/ battery-driven field boost ✓
 - Mounted outboard of main bearing ✓
- PERMANENT MAGNET EXCITEREighteen pole exciter ✓
 - Magnetically coupled DC current ✓
 - Mounted outboard of main bearing ✓
- REGULATION..... Solid-state ✓
 - ±1% regulation ✓

GENERATOR FEATURES

- Four pole, revolving field generator, directly connected to the engine shaft through a heavy-duty, flexible disc for permanent alignment.
- Generator meets the temperature rise standards for class "F" insulation as defined by NEMA MG1-32.6, while the insulation system meets the requirements for the higher class "H" rating.
- All prototype models have passed a three-phase symmetrical short circuit test to assure system protection and reliability.
- All prototype models are tested for motor starting ability by measuring the instantaneous voltage dip with a waveform data acquisition system.
- All models utilize an advanced wire harness design for reliable interconnection within the circuitry.
- Magnetic circuit, including amortisseur windings, tooth and skewed stator design, provides a minimal level of waveform distortion and an electromagnetic interference level which meets accepted requirements for standard AM radio, TV, and marine radio telephone applications.
- Voltage waveform deviation, total harmonic content of the AC waveform, and T.I.F. (Telephone Influence Factor) have been evaluated to acceptable standards in accordance with NEMA MG1-32.
- Alternator is self-ventilated and drip-proof constructed.
- Fully life-tested protective systems, including "field circuit and thermal overload protection" and optional main-line circuit breakers capable of handling full output capacity.
- System Torsional acceptability confirmed during Prototype Testing.

ENGINE SPECIFICATIONS

MAKE	GENERAC
MODEL	3.9DTA
CYLINDERS	4 in-line
DISPLACEMENT	3.9 Liter (238 cu.in.)
BORE	104 mm (4.09 in.)
STROKE	115 mm (4.52 in.)
COMPRESSION RATIO	16.5:1
INTAKE AIR	Turbocharged/Aftercooled
NUMBER OF MAIN BEARINGS	5
CONNECTING RODS	4-Drop Forged Steel
CYLINDER HEAD	Cast Iron Overhead Valve
PISTONS	4- Aluminum Alloy
CRANKSHAFT	Hardened, Steel

VALVE TRAIN

LIFTER TYPE	Solid
INTAKE VALVE MATERIAL	Special Heat Resistant Steel
EXHAUST VALVE MATERIAL	Special Heat Resistant Steel
HARDENED VALVE SEATS	Replaceable

ENGINE GOVERNOR

- MECHANICAL (Gear Driven)
 Standard |
- FREQUENCY REGULATION, NO-LOAD TO FULL LOAD
 5.0% |
- STEADY STATE REGULATION
 ±0.33% |
- ELECTRONIC
 Optional |
- FREQUENCY REGULATION, NO-LOAD TO FULL LOAD
 Isochronous |
- STEADY STATE REGULATION
 ±0.25% |

LUBRICATION SYSTEM

TYPE OF OIL PUMP	Gear
OIL FILTER	Full flow, Cartridge
CRANKCASE CAPACITY	18 Litres (19 qts.)
OIL COOLER	Oil to water

COOLING SYSTEM

TYPE OF SYSTEM	Pressurized, Closed Recovery
WATER PUMP	Pre-Lubed, Self-Sealing
TYPE OF FAN	Pusher
NUMBER OF FAN BLADES	7
DIAMETER OF FAN	457 mm (18 in.)
COOLANT HEATER	120V, 1800 W

FUEL SYSTEM

FUEL	#2D Fuel (Min Cetane #40)
	(Fuel should conform to ASTM Spec.)
FUEL FILTER	Single Cartridge
FUEL INJECTION PUMP	Stanadyne
FUEL PUMP	Mechanical
INJECTORS	Multi-Hole, Nozzle Type
ENGINE TYPE	Direct Injection
FUEL LINE (Supply)	7.94 mm (0.31 in.)
FUEL RETURN LINE	6.35 mm (0.25 in.)
STARTING AID	Glow Plugs

ELECTRICAL SYSTEM

BATTERY CHARGE ALTERNATOR	30 Amps at 24 V
STARTER MOTOR	24 V
RECOMMENDED BATTERY	(2)—12 Volt, 90 A.H., 4DLT
GROUND POLARITY	Negative

Rating definitions - Standby: Applicable for supplying emergency power for the duration of the utility power outage. No overload capability is available for this rating. (All ratings in accordance with BS5514, ISO3046 and DIN6271). Prime (Unlimited Running Time): Applicable for supplying electric power in lieu of commercially purchased power. Prime power is the maximum power available at variable load. A 10% overload capacity is available for 1 hour in 12 hours. (All ratings in accordance with BS5514, ISO3046, ISO8528 and DIN6271).

SD080

OPERATING DATA

	STANDBY		PRIME	
	SD080		SD080	
GENERATOR OUTPUT VOLTAGE/KW-60Hz		Rated AMP		Rated AMP
120/240V, 1-phase, 1.0 pf	80	333	64	267
120/208V, 3-phase, 0.8 pf	80	278	64	222
120/240V, 3-phase, 0.8 pf	80	241	64	192
277/480V, 3-phase, 0.8 pf	80	120	64	96
600V, 3-phase, 0.8 pf	80	96	64	77
GENERATOR OUTPUT VOLTAGE/KVA-50Hz		Rated AMP		Rated AMP
110/220V, 1-phase, 1.0 pf	64	291	51	233
115/200V, 3-phase, 0.8 pf	80	231	64	185
100/200V, 3-phase, 0.8 pf	80	231	64	185
231/400V, 3-phase, 0.8 pf	80	115	64	92
480V, 3-phase, 0.8 pf	80	96	64	62
MOTOR STARTING KVA				
Maximum at 35% instantaneous voltage dip with standard alternator; 50/60 Hz	120/208/240V	277/480V	120/208/240V	277/480V
with optional alternator; 50/60 Hz	137/164	161/193	137/164	161/193
	234/281	276/331	234/281	276/331
FUEL				
Fuel consumption—60 Hz	Load	100%	80%	100%
	gal./hr.	5.5	4.6	4.4
	liters/hr.	20.8	17.3	16.7
Fuel consumption—50 Hz	gal./hr.	4.6	3.8	3.7
	liters/hr.	17.3	14.3	13.8
Fuel pump lift		36"		36"
COOLING				
Coolant capacity	System - lit. (US gal.)	15.9 (4.2)		15.9 (4.2)
	Engine - lit. (US gal.)	6.4 (1.7)		6.4 (1.7)
	Radiator - lit. (US gal.)	9.5 (2.5)		9.5 (2.5)
Coolant flow/min.	60 Hz - lit. (US gal.)	128 (34)		128 (34)
	50 Hz - lit. (US gal.)	107 (28)		107 (28)
Heat rejected to coolant 60 Hz full load	BTU/hr.	220,700		176,500
Heat rejected to coolant 50 Hz full load	BTU/hr.	183,900		147,100
Heat rejected to charge air cooler 60 Hz full load	BTU/hr.	44,300		35,440
Heat rejected to charge air cooler 50 Hz full load	BTU/hr.	36,915		29,532
Inlet air to radiator	60 Hz - m ³ /min. (cfm)	204 (7,200)		204 (7,200)
	50 Hz - m ³ /min. (cfm)	170 (6004)		170 (6004)
Max. operating air temp to radiator *see note	°C (°F)	60 (140)		60 (140)
Max. operating ambient temp *see note	°C (°F)	50 (122)		50 (122)
COMBUSTION AIR REQUIREMENTS				
Flow at rated power	60 Hz - cfm	272		220
	50 Hz - m ³ /min.	6.1		4.9
EXHAUST				
Exhaust flow at rated output	60 Hz -m ³ /min. (cfm)	21.3 (754)		17.0 (603)
	50 Hz - m ³ /min. (cfm)	17 (600)		14 (494)
Max recommended back pressure	"Hg	1.5		1.5
Exhaust temperature 60 Hz (full load)	°C (°F)	566 (1050)		496 (924)
Exhaust outlet size		3"		3"
ENGINE				
Rated RPM	60 / 50 Hz	1800 / 1500		1800 / 1500
HP at rated KW	60 / 50 Hz	120 / 95		97 / 76
Piston speed	60 Hz - m/min. (ft./min.)	414 (1358)		414 (1358)
	50 Hz - m/min. (ft./min.)	345 (1132)		345 (1132)
BMEP	60 / 50 Hz - psi	222 / 211		179 / 170
POWER ADJUSTMENTS FOR AMBIENT CONDITIONS				
Temperature	-4.5% for every 10°C above - °C	40		40
	-2.5% for every 10°F above - °F	104		104
Altitude	-0.8% for every 100 m above - m	1524		1524
	-2.5% for every 1000 ft. above - ft.	5000		5000


*Note: Values given are maximum temperatures to which power adjustments can be applied. Consult your Generac Power System representative if operating exceed these maximums.

- High Coolant Temperature Automatic Shutdown
- Low Coolant Level Automatic Shutdown
- Low Oil Pressure Automatic Shutdown
- Overspeed Automatic Shutdown (Solid-state)
- Crank Limiter (Solid-state)
- Oil Drain Extension
- Radiator Drain Extension
- Factory-Installed Cool Flow Radiator
- Closed Coolant Recovery System
- UV/Ozone Resistant Hoses
- Rubber-Booted Engine Electrical Connections
- Secondary Fuel Filter
- Fuel Lockoff Solenoid
- Stainless Steel Flexible Exhaust Connection
- Battery Charge Alternator
- Battery Cables
- Battery Tray
- Vibration Isolation of Unit to Mounting Base
- 24 Volt, Solenoid-activated Starter Motor
- Air Cleaner
- Fan Guard
- Control Console
- Radiator Duct Adapter
- Coolant Heater

OPTIONS

- **OPTIONAL COOLING SYSTEM ACCESSORIES**
 - 208/240V Coolant Heater
- **OPTIONAL FUEL ACCESSORIES**
 - Flexible Fuel Lines
 - UL Listed Fuel Tanks
 - Base Tank Low Fuel Alarm
 - Primary Fuel Filter
 - Primary Fuel Filter with Heater
- **OPTIONAL EXHAUST ACCESSORIES**
 - Critical Exhaust Silencer (Standard on enclosed gensets)
- **OPTIONAL ELECTRICAL ACCESSORIES**
 - Battery, 12 Volt, 135 A.H., 4DLT
 - 2A Battery Charger
 - 10A Dual Rate Battery Charger
 - Battery Heater
- **OPTIONAL ALTERNATOR ACCESSORIES**
 - Alternator Upsizing
 - Alternator Strip Heater
 - Alternator Tropicalization
 - Voltage Changeover Switch
 - Main Line Circuit Breaker
- **CONTROL CONSOLE OPTIONS**
 - Digital Controller H100 (Bulletin 0172110SBY)
- **ADDITIONAL OPTIONAL EQUIPMENT**
 - Automatic Transfer Switch
 - Isochronous Governor
 - 3 Light Remote Annunciator
 - 5 Light Remote Annunciator
 - 20 Light Remote Annunciator
 - Remote Relay Panels
 - Unit Vibration Isolators (Pad/Spring)
 - Oil Make-Up System
 - Oil Heater
 - 5 Year Warranties
 - Export Boxing
 - GenLink® Communications Software
- **OPTIONAL ENCLOSURE**
 - Weather Protective
 - Sound Attenuated
 - Aluminum and Stainless Steel
 - Enclosed Muffler

Distributed by:



mm [in]

GENERAC® POWER SYSTEMS, INC. • P.O. BOX 8 • WAUKESHA, WI 53187
 262/544-4811 • FAX 262/544-4851