1 of 2

GENERAC[®]

XC6500

XC SERIES Commercial Portable Generators

Features

- X Frame fully wrapped, heavy duty 12 gauge steel tube provides rugged durability and protects the generator and fuel tank from damage.
- Steel lifting pocket designed for easier lifting and transportation on jobsites by crane or forklift.
- **Generac G-Force engine** features Best-in-Class power with full pressure lubrication and is optimized for generator use.
- Impact resistant fuel tank design recessed tank edges reduce damage when transported by forklift.
- Full panel GFCI protection OSHA compliant with covered outlets to protect from the elements.
- Easy access to all routine maintenance areas including filters and spark plugs; no need to remove fuel tank or side panels.
- Never flat wheels with steel hubs makes movement around the jobsite easy and efficient.
- · Protected axle integrated into frame, shields from impact during transport.
- Welded steel feet reinforced for superior durability.
- **Fold-down locking handles** feature one-handed locking mechanism for easy storage.
- Engraving plate allows unit to be tagged / cataloged for use in contractor and rental fleets.
- **TruePower™ Technology** provides clean, smooth operation of sensitive electronics, tools, and appliances.


Model 6823-0 UPC: 696471070903 (EPA/49-State/CSA-Canada)

Model 6824-0 UPC:696471070910 (EPA/CARB-California)



AC Rated Output Running Watts 6500 AC Maximum Output Starting Watts 8125

Control Panel



XC6500

Specifications

| Product Series | XC6500 | |
|------------------------------------|---------------------------|--|
| Model (Configuration) | 6823-0 | |
| | (EPA/49-State/CSA-Canada) | |
| | 6824-0 (EPA/CARB-Cali- | |
| | fornia) | |
| AC Rated Output Running Watts | 6500 | |
| AC Maximum Output Starting Watts | 8125 | |
| Rated AC Voltage | 120/240 VAC | |
| Rated AC Frequency | 60 Hz | |
| Rated 120/240 VAC Amperage | 54.2/27.0 | |
| Engine Displacement | 426cc | |
| Engine Type | Generac G-Force | |
| Engine RPM | 3600 | |
| Recommended Oil | 10W-30 / SAE 30 | |
| Lubrication Method | Oil Pump | |
| Automatic Voltage Regulation (AVR) | Yes | |
| Total Harmonic Distortion | < 5% | |
| Choke Location | On Engine | |
| Fuel Shut Off | On Fuel Tank | |
| Starting Method | Recoil Pull Start | |
| Low Oil Shutdown | Low Pressure | |
| Neutral Bonded to Ground | Yes | |
| Start Switch Type | Run/Stop | |
| Switch Location | On Control Panel | |

| Steel Lifting Pocket | Included | |
|-------------------------------|--------------------------|--|
| Fuel Gauge | Built-in Tank | |
| Fuel Tank Capacity Gal (Ltrs) | 8.5 (32) | |
| Run Time at 50% (Hours) | 14 | |
| Handle Style | Dual Folding/Locking | |
| Grab Bars | Yes | |
| Wheel Type | 10" Solid with Steel Hub | |
| Maintenance Kit | ince Kit Included | |
| Warranty- Commercial | 2 Year Limited | |
| Warranty- Residential | 3 Year Limited | |
| | | |

Dimensions and Weights

| Model | 6823-0 | 6824-0 |
|--------------------------|-------------|--------|
| Length in (mm) | 34.3 (872) | |
| Width in (mm) | 28.6 (727) | |
| Height in (mm) | 32.5 (825) | |
| Extended Length in (mm) | 46.8 (1188) | |
| Carton Length in (mm) | 38.8 (984) | |
| Carton Width in (mm) | 23.5 (597) | |
| Carton Height in (mm) | 30 (762) | |
| Unit Weight lbs (kg) | 243 (110.2) | |
| Shipping Weight lbs (kg) | 263 (119.3) | |

