

OneWASH™

Power Washers



2000-3000 psi - Model 006412-0 (49-State & Canada)
UPC: 696471064124

Model 006414-0 (50-State)
UPC: 696471064148



FEATURES

VERSATILITY

- **PowerDial™** provides total control at the turn of a dial. Easily adjust the intensity of the spray to clean a wide range of different surfaces like automobile finishes, aluminum and vinyl siding, decks and fences and the toughest brick and concrete, all with a single, easy-to-use control.

EASE OF USE

- **Automatic System Protection** constantly monitors the oil and water level. If the oil or water runs low, the LED System Alert activates and automatically cuts power to the unit to protect it from damage.
- **Consolidated Control Panel** has all your controls in one easily accessible location.
- **Horizontal Axial Cam Pump** makes hose connections a snap.
- **Folding/Nesting Handle** provides compact storage.
- **Drainable Detergent Tank** allows for easily flushing chemicals from tank after each use.

POWER

- **Generac® 212cc OHV Engine** is the largest, most powerful engine in its class.
- Horizontally mounted engine and pump for improved system lubrication.

COMFORT

- **Comfort-Grip Handle** provides greater comfort for ease of use.
- **Ergonomic Inverted Trigger** reduces user fatigue.

MOBILITY

- **Wide, Never-Go-Flat 11" Wheels** provide easy transport regardless of terrain.
- **Precision Balanced** for stability and effortless mobility.

2000-3000 psi

specifications

PRESSURE AND FLOW

Outlet Pressure (psi/bar)	2000-3000/138-207
Flow Rate (gpm)/(L/min)	2.8/10.6

ENGINE

Manufacturer	Generac
Displacement (in³/cc)	12.9/212
Type	OHV (Overhead Valve)
Orientation	Horizontal
Low Oil Shutdown System	Yes
Fuel Capacity (gal/L)	0.8/3
Fuel On/Off Switch	Yes
Oil Capacity (oz/L)	20/0.6
Recommended Engine Oil	SAE 30 or 10W30
Throttle Control	Manual
Choke	Manual
Starting Method	Manual

PUMP

Type	Axial Cam
Plunger	Stainless Steel
Material	Aluminum body, brass head
Maximum Water Supply Temperature (°F/°C)	100/38

HOSE

Length (ft/m)	30/9.1
Diameter (in/mm)	.25/6.4
Rating (psi/bar)	3100/213
Connectors	M22 threaded

DETERGENT SYSTEM

Number of Chemical Tanks per Unit	1
Chemical Tank Description	3/4 gallon (2.8 liters)

NOZZLES

Number of Nozzles per Unit	3
Nozzle Descriptions	0, 25, soap

GUN & LANCE

Gun	Ergonomic
Gun to Lance Connection	M22 threaded
Gun to Hose Connection	M22 threaded
Lance Length (in/cm)	20/50.8
Lance to Nozzle Connection	Quick change
Lance Material	Chrome-plated steel
Lance Connector Material	Brass

FRAME & MISC.

Handle	Folding
Frame Construction	Welded steel
Wheels (in/cm)	2.5 x 11/6.4 x 27.9 never flat

DIMENSIONS & WEIGHTS

Length (in/cm)	20.6/52.3
Width (wheel to wheel, in/cm)	21/53.3
Height (in/cm)	39.5/100.3
Weight Including Hose, Gun & Lance (lb/kg)	68.5/31.1
Boxed Weight (lb/kg)	75/34
Boxed Length (in/cm)	22.5/57.2
Boxed Width (in/cm)	22.5/57.2
Boxed Height (in/cm)	22.5/57.2

WARRANTY

Warranty	2 year limited
----------	----------------