



Power Washer



2900 psi - Model G008874 (50-State & Canada) UPC: 696471079517



FEATURES

POWERFUL GENERAC OHV ENGINE

Delivers maximum cleaning performance and reliability

AXIAL CAM PUMP WITH EASY-ACCESS HOSE CONNECTIONS

Prevents kneeling down on the ground

ERGONOMIC SPRAY GUN

 Molded grip, easy-to-pull trigger, and rear hose connection for comfort during prolonged use

NEVER-FLAT TIRES

Improved mobility on rugged terrain

QUICK CONNECT NOZZLE TIPS

Easily change the intensity of the spray to suit the application

COMPACT DESIGN

 Minimum storage space required in the garage or shed 2 of 2



specifications 2900 psi

PRESSURE AND FLOW

Max Outlet Pressure (psi/bar)	2900/200
Max Flow Rate (gpm)/(L/min)	2.4/9.0

ENGINE

Manufacturer	Generac
Displacement (in³/cc)	11.9/196
Туре	4 cycle/OHV
Orientation	Horizontal
Low Oil Shutdown System	No
Fuel Capacity (gal/L)	0.8/3
Fuel On/Off Switch	Yes
Oil Capacity (oz/L)	20/0.6
Recommended Engine Oil	10W-30/SAE 30
Throttle Control	Fixed Speed
Choke	Manual
Starting Method	Recoil Pull Start

PUMP

Туре	Axial Cam
Maximum Water Supply Temperature (°F/°C)	100/38

HOSE

Length (ft/m)	25/7.6
Diameter (in/mm)	0.25/6.4
Rating (psi/bar)	3100/214
Connectors	M22 Threaded

NOZZLES

Nozzle Descriptions	0°, 25°, 40°, Soap
---------------------	--------------------

GUN & LANCE

Gun Type	Ergonomic
Gun to Lance Connection	M22 Threaded
Gun to Hose Connection	M22 Threaded
Lance Length (in/cm)	20/51
Lance to Nozzle Connection	Quick Change

FRAME & MISC.

Handle	Fixed - Click In
Frame Construction	Steel
Wheels (in/cm)	1.75/4.4 x 10/25.4 Never Flat

DIMENSIONS & WEIGHTS

Length (in/cm)	24.4/62
Width (wheel to wheel, in/cm)	18.9/47.9
Height (in/cm)	35.5/90.2
Unit Weight (lbs/kg)	57/25.85
Boxed Length (in/cm)	24/61
Boxed Width (in/cm)	20/51
Boxed Height (in/cm)	22/56
Boxed Weight (lb/kg)	72/33

WARRANTY

Warranty	2 Year Limited

