

T20-S

Trash Pump

Model 6920-1 (49ST/Canada)
UPC: 696471069204



FEATURES

- Powerful Generac Pump - Can pump up to 185 gallons per minute
- Durable design - Silicon Carbide Seal, Cast Iron Volute and Impeller
- Extended run-time fuel tank with fuel gauge
- On-board instructions for easier set up and starting
- Color coded suction and discharge ports to ensure the correct hose connections
- Powerful Generac G-Force 211cc OHC engine with low oil alert provides longer engine life

Specifications

Engine Type	4 cycle/OHC
Engine Displacement (cc)	211
Start Type	Recoil Pull Start
Low Oil Shutdown Method	Low Level
Recommended Oil	10W-30 / SAE30
Fuel Capacity (gal/L)	3.04/11.5
Max Run Time	5.0 hrs
Flow gpm/lpm	185/700
Max Total Head (ft/m)	98/29.9
Max Suction Lift (ft/m)	26/7.9
Mechanical Seal Type	Silicon Carbide
Solid Handling (in)	1
Suction Port (NPT)	2.0
Discharge Port (NPT)	2.0
Pump Housing	Aluminum
Impeller	Ductile Cast Iron
Volute	Ductile Cast Iron

Hose Kit Included	N/A
Discharge Hose Length (ft/m)	N/A
Suction Hose Length (ft/m)	N/A
Hose Connections	N/A
Strainer	N/A
Wheel Kit	N/A
Country of Origin	China
Warranty	3 Year Limited
Length (L) (in/mm)	26.6/675
Width (W) (in/mm)	19.9/505
Height (H) (in/mm)	22.8/580
Unit Weight (lb/kg)	109.1/49.5
Carton Length (in/mm)	27.2/692
Carton Width (in/mm)	20.5/520
Carton Height (in/mm)	23.7/602
Shipping Weight (lb/kg)	117.5/53.3

