

Power Washers

Electric Start

1 of 2

Model G0088940: (49 State & Canada) UPC: 696471084306 Model G0088941: (50 State & Canada) UPC: 696471086669



FEATURES

ERGONOMIC SPRAY GUN

Inverted trigger with cushion grip for extended use ۲

POWERFUL GENERAC OHV ENGINE

- Delivers maximum cleaning performance and reliability
- Longer run time large 0.8 gallon fuel tank

AXIAL CAM PUMP WITH EASY-ACCESS HOSE **CONNECTIONS**

Prevents kneeling down on the ground

ELECTRIC START

- One touch push button start
- Long lasting lithium-ion battery will provide up to 50 starts

COMPACT DESIGN

Minimum storage space required in the garage or shed





Specifications

PRESSURE AND FLOW

THEODORE AND TEOM	
Max Outlet Pressure (psi/bar)	3100/214
Max Flow Rate (gpm)/(L/min)	2.5/9.5

ENGINE

Generac
196
4 cycle/OHV
Horizontal
Splash
No
0.8/3.0
Yes
20/0.6
10W-30/SAE 30
Fixed Speed
Manual
Electric/Recoil Pull Start

DETERGENT SYSTEM

Chemical Tank	Yes
Chemical Tank Size (gal/L)	0.6/2.3

NOZZLES

	Nozzle Descriptions	0°, 25°, 40°, Soap
--	---------------------	--------------------

GUN & LANCE

Gun Type	Ergonomic
Gun to Lance Connection	M22
Gun to Hose Connection	M22
Lance Length (in/cm)	20/51
Lance to Nozzle Connection	Quick Change

FRAME & MISC.

Handle	Fixed - Click In
Frame Construction	Steel Welded
Wheels - Never Flat (in/cm)	1.75/4.4 x 10/25.4

DIMENSIONS & WEIGHTS

Length (in/cm)	24.4/61.0
Width (wheel to wheel, in/cm)	19/48.3
Height (in/cm)	35.5/90.2
Unit Weight (lbs/kg)	59/27
Boxed Length (in/cm)	24/61.0
Boxed Width (in/cm)	20/50.8
Boxed Height (in/cm)	22/56.0
Boxed Weight (lb/kg)	70/32

WARRANTY

	Warranty	3 Year Limited
--	----------	----------------



Generac Power Systems, Inc. • S45 W29290 HWY. 59, Waukesha, WI 53189 • generac.com

©2021 Generac Power Systems, Inc. All rights reserved. All specifications are subject to change without notice. Part No. A0001696417-B 10/28/2021

PUMP

Туре	Axial Cam
Material	Aluminum
Maximum Water Supply Temperature (°F/°C)	100/38

HOSE

Туре	PVC
Length (ft/m)	25/7.6
Diameter (in/mm)	0.25/6.4
Rating (psi/bar)	3100/214
Connectors	M22