

Commercial Power Washers

GENERAC® | **PRO**

COMMERCIAL POWER WASHERS 3300–3600 psi



Model and UPC

G008870-0 – 3300 psi (49-State & Canada) – UPC: 696471079630
G008871-0 – 3600 psi (49-State & Canada) – UPC: 696471079838
G008870-1 – 3300 psi (50-State & Canada) – UPC: 696471086812
G008871-1 – 3600 psi (50-State & Canada) – UPC: 696471086829



*Assembled in the USA using domestic and foreign parts

FEATURES

- **POWER:** The powerful Generac® G-Force OHV engine delivers maximum cleaning performance and reliability. Low-oil shutdown protects the engine.
- **DURABILITY:** Commercial Grade Direct Drive AR® Triplex Pumps - Up to 4X longer life than axial cam pumps. The rugged frame is 1.25 in (31.8 mm) welded steel tube with a 12 gauge formed steel baseplate. The 25 ft (7.6 m) steel reinforced hose is durable and non-marring, so it will not leave scuff marks.
- **EASY-TO-USE:** Save time with the easy-to-move 3-wheel design that moves with you around the jobsite to prevent downtime. Features an integrated 5 gal (18.9 L) bucket holder for detergent or onboard storage. Save space with the folding handle for compact storage and transport. The pressure control valve allows for adjustable cleaning power.
- **MOBILITY:** Oversized never-flat wheels easily handle rugged jobsite terrain.
- **COMFORT:** The ergonomic spray gun features quick change connections, a stabilizing side handle, a molded grip, and an easy-to-pull trigger for comfort during prolonged use.

3300–3600 psi

PRESSURE AND FLOW	G008870-0	G008871-0
	G008870-1	G008871-1
Maximum outlet pressure (psi / bar)	3,300 / 228	3,600 / 248
Maximum flow rate (gpm) / (L/min)	3.0 / 11.4	2.6 / 9.8

ENGINE

Manufacturer	Generac
Displacement (in ³ / cc)	12.9 / 212
Type	4 cycle / OHV
Orientation	Horizontal
Lubrication method	Splash
Low oil shutdown system	Yes
Fuel capacity (gal / L)	0.8 / 3
Fuel ON/OFF valve	Yes
Oil capacity (oz / L)	20 / 0.6
Recommended engine oil	10W-30 / SAE 30
Throttle control	Manual
Choke	Manual
Starting method	Manual/recoil

PUMP

Type	Triplex
Manufacturer	AR
Plunger	Aluminum / brass
Maximum water supply temperature (°F / °C)	100 / 38

HOSE

Type	Polyurethane, cloth braided
Length (ft / m)	25 / 7.62
Diameter (in / mm)	0.3125 / 7.9
Rating (psi / bar)	4,000 / 276
Connectors	Quick change

DETERGENT SYSTEM

Chemical tank	No
Chemical tank description	5 gal (18.9 L) detergent bucket holder

NOZZELS & DETERGENT

Number of nozzles per unit	5
Nozzle descriptions	0°, 15°, 25°, 40°, Soap

GUN & LANCE

Gun type	Professional
Gun to lance connection	M22
Gun to hose connection	Quick connect
Lance length (in / cm)	29 / 74
Lance material	Stainless steel
Lance to nozzle connection	Quick change

FRAME & MISC.

Handle	Folding
Frame construction	1.25 in (31.8 mm) welded steel tube
Wheels (in / mm)	3 x 10 (76.2 x 254) Never Flat

DIMENSIONS & WEIGHTS

Storage unit length (in / cm)	37.9 / 96.3
Extended unit length (in / cm)	51.5 / 130.9
Unit width (wheel to wheel, in / cm)	23.3 / 59.2
Storage unit height (in / cm)	27.6 / 70.1
Extended unit height (in / cm)	32.5 / 82.5
Unit weight (lbs / kg)	104 / 47.2
Boxed length (in / cm)	40.0 / 101.6
Boxed width (in / cm)	27.0 / 68.6
Boxed height (in / cm)	32.8 / 83.2
Boxed weight (lb / kg)	138 / 62.6

WARRANTY

Commercial	3 year limited
------------	----------------