

# Mobile Generator – MMG120 Specifications

#### ENGINE

- John Deere® PE4045HF285 turbocharged, diesel engine
  - o Prime 144 hp @ 1800 rpm
  - Standby 158 hp @ 1800 rpm
  - o 4 cylinder
  - o 4.5 L displacement
  - o Tier III approved
- Steel, single wall fuel tank
  - o 342 gal. capacity
  - o 44 hr. run time full load
  - Fuel tank built into skid of generator set
- Fuel consumption at prime:
  - o 100% 7.4 gph (28.0 Lph)
  - o 75% 5.6 gph (21.2 Lph)
  - o 50% 3.7 gph (14.0 Lph)
- Cooling system capable of operating at 120°F ambient
- Low coolant shutdown
- Radiator and oil drains plumbed to exterior
- Rubber vibration dampers isolate engine/generator from frame
- Disposable air filter paper element
- Air filter restriction indicator mounted on control panel
- 60 Hz engine/generator
- Electronic isochronous governing

#### GENERATOR


- Marathon Electric<sup>®</sup>
  - o Brushless
  - o 4 pole
  - Class H insulation
- Voltage regulation +/- 1% with Marathon SE350 Voltage Regulator

#### SYSTEM OUTPUT

- 3 selector switch modes:
  - Single phase 120 / 240V Zig Zag
  - Three phase 120 / 208V Low Wye
  - Three phase 277 / 480V High Wye
- 91 kW / 91 kVA standby, single phase
- 85 kW / 85 kVA prime, single phase
- 102 kW / 127 kVA standby, three phase
- 93 kW / 116 kVA prime, three phase

#### SYSTEM CONTROLS

- Microprocessor-based controller
  - Backlit, 128x64 pixel resolution display
  - o -40°F to 185°F operating temperature range
  - o Thermostatically controlled LCD heater



0

0


- Six LED indicators w/ lamp test
  - Alarm / Fault (Red)
  - Ready / Manual (Red)
  - Running (Green)
  - Warning (Yellow)
  - Ready / Auto (Green)
  - Supplying Load (Green)
- Push buttons for easy operation
  - o Manual or Auto Start
  - o Engine Start or Stop
  - o Alarm Cancel & Fault Reset
    - Scrolling Arrows for Diagnostic Information
      - System kW output display
        - Line output & frequency display
        - Engine diagnostic display
          - Oil pressure
          - Engine temperature
          - Fuel level
          - Battery
        - System hours
          - Running hours
            - kW hours
          - Time to service
    - Alarm list warnings / shutdowns are date & time stamped
      - ♦ Fuel level: warning 15%; shutdown 5%
      - Overspeed protection: shutdown 115%
      - Oil pressure: warning 25 psi; shutdown 20 psi
      - Coolant temperature: warning 220°F; shutdown 230°F
      - ♦ Battery voltage: over 15VDC; under 11VDC
      - Generator over voltage: warning 110%; shutdown 111%
      - Generator under voltage: warning 87%; shutdown 86%
      - Generator over frequency: warning 105%; shutdown 110%
      - Generator under frequency: warning 95%; shutdown 90%
      - Over current shutdown

#### **ELECTRICAL CONTROLS**

.

- Remote start / stop contacts located next to lug box
- Lockable control box door with diagnostics window
- Lockable lug box with safety switch
  - Trips main breaker when lug door is opened
  - o Disables voltage regulator
  - Cable entry guides to the lug box
    - Restricts access of foreign objects
- Output ground connection lug inside lug box
- Convenience receptacles with individual breakers (restricted use in high wye mode)
  - (2) 120V 20 Amp GFCI duplex outlets (Nema 5-20R type)
  - o (3) 125 / 250V 50 Amp, 3 pole, 4 wire twistlock (Non-Nema 6369)
- Panel mounted rheostat for voltage adjustment +/- 10%
- 1000 CCA wet cell battery





#### **ENCLOSURE**

- Generac Mobile Power decals
- Aluminum, sound attenuated enclosure
  - o UV & fade resistant, high temperature cured, white polyester powder paint
  - o Insulated and baffled
  - o 68 dB(A) at 23 feet prime power
- Fully lockable enclosure including doors and fuel fill
- Stainless steel hinges on doors
- Emergency stop switch located on outside of enclosure
- Central lifting point
- Multi-lingual operating/safety decals
- Document holder with operating manual including AC/DC wiring diagrams

#### TRAILER

- DOT approved tail, side, brake, and directional lights
  Recessed rear lights
- Transportation tie downs
- Safety chains with spring loaded safety hooks
- 3" lunette ring hitch
- (2) 6000 lb. axles with surge brakes
- 5000 lb. tongue jack with footplate
- 7.50x16E-6-W tubeless tires 10 ply

## **WEIGHTS & DIMENSIONS**

Skid mounted

- Dry weight: 5429 lbs (2463 kg)
- Operating weight: 7914 lbs (3590 kg)
- 132 x 50 x 77 in
  - (3.35 x 1.27 x 1.95 m)

Trailer mounted

- Dry weight: 6825 lbs (3096 kg)
- Operating weight: 9310 lbs (4223 kg)
- 210 x 86 x 93 in
- (5.33 x 2.18 x 2.36 m)

#### WARRANTY

• Engine and generator covered under OEM warranty – consult factory for details.

### CERTIFICATIONS

CSA certified

# MMG 120 Options

#### **ENGINE OPTIONS**

- In-line engine block heater (Kim Hotstart)
- Fuel transfer pump

#### ELECTRICAL CONTROLS OPTIONS

- Battery disconnect
- Battery charger 2A trickle

#### **GENERATOR OPTIONS**

• Super Start Generator - motor starting applications

#### **VOLTAGE OUTPUT OPTIONS**

- 4 position phase switch
  - Single phase 120 / 240V Zig Zag
  - Three phase 120 / 208V Low Wye
  - Three phase 277 / 480V High Wye
  - Three phase 120 / 240V Delta
- Dedicated voltage configurations
- Buck Transformer kit Provides 120V at GFCI outlets when in 277/480V
- Cam locks

#### SYSTEM CONTROLS OPTIONS

• Auxiliary strobe/audible indication for soft & hard alarm conditions

#### **COOLANT OPTIONS**

• 60/40 Coolant - cold weather applications

#### **ENCLOSURE OPTIONS**

- Fire extinguisher
- Interior cabinet light
- Control panel light

#### **FUEL TANK OPTIONS**

 23 hr. double wall fuel tank 120% Containment

#### **TRAILER OPTIONS**

- Tandem axle trailer w/ electric brakes
- 6 pin or 7 spade electrical connectors
- Spare tire/wheel kit

#### **HITCH OPTIONS**

◆ 2 5/16" ball