

PROTECTOR® SERIES Standby Generators

Liquid-Cooled Gaseous Engine

Protector® Series

INCLUDES:

- Two-Line LCD Multilingual Digital Evolution™ Controller (English/Spanish/French/Portuguese)
- Isochronous Electronic Governor
- Sound Attenuated Enclosure
- Closed Coolant Recovery System
- Smart Battery Charger
- UV/Ozone Resistant Hoses
- Voltage and Frequency Regulation Designed for Sensitive Electronics
- 5 Year Limited Warranty
- UL 2200 Listed

Standby Power Rating Model RG10090 (Aluminum - Bisque) - 100 kW 60 Hz











Meets EPA Emission Regulations CA / MA Emission Compliant

FEATURES

- INNOVATIVE DESIGN & PROTOTYPE TESTING are key components of GENERAC'S success in "IMPROVING POWER BY DESIGN." But it doesn't stop there. Total commitment to component testing, reliability testing, environmental testing, destruction and life testing, plus testing to applicable CSA, NEMA, EGSA, and other standards, allows you to choose GENERAC POWER SYSTEMS with the confidence that these systems will provide superior performance.
- O TEST CRITERIA:
 - ✓ PROTOTYPE TESTED
 ✓ NEMA MG1-22 EVALUATION
 ✓ SYSTEM TORSIONAL TESTED
 ✓ MOTOR STARTING ABILITY
- MOBILE LINK® CONNECTIVITY: Free with select Protector Series standby generator sets, Mobile Link Wi-Fi allows users to monitor the generator set status from anywhere in the world using a smartphone, tablet, or PC. Easily access information such as the current operating status and maintenance alerts. Users can connect an account to an authorized service dealer for fast, friendly, and proactive service. With Mobile Link, users are taken care of before the next power outage.

O SOLID-STATE, FREQUENCY COMPENSATED VOLTAGE REGULATION.

This state-of-the-art power maximizing regulation system is standard on all Generac models. It provides optimized FAST RESPONSE to changing load conditions and MAXIMUM MOTOR STARTING CAPABILITY by electronically torque-matching the surge loads to the engine.

- SINGLE SOURCE SERVICE RESPONSE from Generac's extensive dealer network provides parts and service know-how for the entire unit, from the engine to the smallest electronic component.
- GENERAC TRANSFER SWITCHES. Long life and reliability are synonymous with GENERAC POWER SYSTEMS. One reason for this confidence is the GENERAC product line is offered with its own transfer systems and controls for total system compatibility.





2 of 7

GENERAC

100 kW

application & engineering data

GENERATOR SPECIFICATIONS

| | 100 kW |
|-------------------------------------|-----------------------|
| Туре | Synchronous |
| Rotor Insulation Class | Н |
| Stator Insulation Class | Н |
| Telephone Interference Factor (TIF) | < 50 |
| Alternator Output Leads 1-Phase | 4 wire |
| Alternator Output Leads 3-Phase | 12 wire |
| Bearings | Sealed Ball |
| Coupling | Flexible Disc |
| Excitation System | Synchronous Brushless |
| Total Harmonic Distortion | <5% |

VOLTAGE REGULATION

| Туре | Full Digital |
|------------|------------------------------------|
| Sensing | All |
| Regulation | Designed for Sensitive Electronics |

GOVERNOR SPECIFICATIONS

| Туре | Electronic |
|-------------------------|------------------------------------|
| Frequency Regulation | Isochronous |
| Steady State Regulation | Designed for Sensitive Electronics |

ELECTRICAL SYSTEM

| Battery Charger Alternator | 40 Amp |
|--|-------------------|
| Static Battery Charger | 2.5 Amp |
| Recommended Battery (battery included) | Group 31, 925 CCA |
| System Voltage | 12 Volts |

GENERATOR FEATURES

Revolving field heavy duty generator Directly connected to the engine Operating temperature rise 135° C above 25° C ambient Class H insulation is NEMA rated All models fully prototyped tested

ENCLOSURE FEATURES

| Aluminum weather protective enclosure | Ensures protection against mother nature. Electrostatically applied textured epoxy paint for added durability. | |
|---------------------------------------|--|--|
| Enclosed critical grade muffler | Quiet, critical grade muffler is mounted inside the unit to prevent injuries. | |
| Small, compact, attractive | Makes for an easy, eye appealing installation. | |
| SAE | Sound attenuated enclosure ensures quiet operation. | |

(All ratings in accordance with BS5514, ISO3046, ISO8528, SAE J1349 and DIN6271)

ENGINE SPECIFICATIONS

| | 100 kW | |
|------------------------------------|---------------------|--|
| Make | Generac | |
| Туре | V | |
| Cylinders | 8 | |
| Displacement - In ³ (L) | 540 (8.86) | |
| Bore (in / mm) | 4.5 / 114.3 | |
| Stroke (in / mm) | 4.25 / 107.95 | |
| Compression Ratio | 9.9:1 | |
| Intake Air System | Naturally Aspirated | |
| Lifter Type | Hydraulic Roller | |

ENGINE LUBRICATION SYSTEM

| Oil Pump Type | Gear |
|-----------------------------|-----------------------------|
| Oil Filter Type | Full Flow Spin-On Cartridge |
| Crankcase Capacity (qt / L) | 10.5 / 9.9 |

ENGINE COOLING SYSTEM

| Туре | Pressurized Closed |
|------------------------|--------------------|
| Water Pump | Belt-Driven |
| Fan Speed (rpm) | 2,330 |
| Fan Diameter (in / cm) | 22 (55.9) |
| Fan Mode | Pusher |

FUEL SYSTEM

| Fuel Type | Natural Gas, Propane Vapor |
|--------------------------|----------------------------|
| Carburetor | Down Draft |
| Secondary Fuel Regulator | Standard |
| Fuel Shut Off Solenoid | Standard |
| LP Fuel Pressure | 11 - 14 in Water Column |
| NG Fuel Pressure | 11 - 14 in Water Column |

GENERA

operating data 100 kW

GENERATOR OUTPUT VOLTAGE/kW - 60 Hz

| | | kW LPG | Amp LPG | kW Nat. Gas | Amp Nat. Gas | CB Size (Both) |
|---------|-----------------------|--------|---------|-------------|--------------|----------------|
| RG10090 | 120/240 V, 1Ø, 1.0 pf | 96 | 400 | 96 | 400 | 400 |
| | 120/208 V, 3Ø, 0.8 pf | 100 | 347 | 96 | 333 | 400 |
| | 120/240 V, 3Ø, 0.8 pf | 100 | 300 | 96 | 288 | 350 |
| | 277/480 V, 3Ø, 0.8 pf | 100 | 150 | 96 | 144 | 175 |

SURGE CAPACITY IN AMPS

ENGINE FUEL CONSUMPTION

| | | Voltage Dip |
|---------|-----------------|-------------|
| | | 30% |
| RG10090 | 120 / 240 V, 1Ø | 854 |
| | 120 / 208 V, 3Ø | 430 |
| | 120 / 240 V, 3Ø | 372 |
| | 277 / 480 V, 3Ø | 244 |

| | | Natural Gas | | Propane | |
|---------|--------------------|---------------|--------------|------------------------|--------------|
| | | (ft^3 / hr) | (m^3 / hr) | (ft ³ / hr) | (m^3 / hr) |
| RG10090 | 25% of rated load | 429 | 12.1 | 141 | 4.0 |
| | 50% of rated load | 667 | 18.9 | 218 | 6.2 |
| | 75% of rated load | 913 | 25.9 | 280 | 7.9 |
| | 100% of rated load | 1,148 | 32.5 | 360 | 10.2 |

Note: Fuel pipe must be sized for full load.

For Btu content, multiply ft^3 / $hr\ x\ 2,520\ (LP)$ or ft^3 / $hr\ x\ 1,000\ (NG)$.

For megajoule content, multiply m³ / hr x 93.15 (LP) or m³ / hr x 37.26 (NG).

Refer to "Emissions Data Sheets" for maximum fuel flow for EPA and SCAQMD permitting purposes.

STANDBY RATING: Standby ratings apply to installations served by a reliable utility source. The standby rating is applicable to varying loads for the duration of a power outage. There is no overload capability for this rating. Ratings are in accordance with ISO-3046-1. Design and specifications are subject to change without notice.

3 of 7



100 kW operating data

| ENGINE COOLING | | 100 kW |
|--|--------------------|---------------------------------|
| Air Flow (Fan Air Flow Across Radiator) - Open Set scfm (m ³ /m | in) | 6,589 (186) |
| System Coolant Capacity (gal / liters) | | 5.5 (20.8) |
| Heat Rejection to Coolant (BTU per hr / MJ per hr) | | Contact Factory |
| Maximum Operation Air Temperature on Radiator (°F / °C) | | Contact Factory |
| Maximum Ambient Temperature (°F / °C) | | 122 (50) |
| COMBUSTION REQUIREMENTS | | |
| Flow at Rated Power scfm (m ³ /min) | | 230 (6.5) |
| SOUND EMISSIONS | | · |
| Sound Output in dB(A) at 23 ft (7 m) With Generator* | | 71 db |
| *In normal operation | | · |
| EXHAUST | | |
| Exhaust Flow at Rated Output scfm (m ³ /min) | | 771 (21.8) |
| Exhaust Temperature (Rated Output) °F (°C) | | 1,350 (732) |
| ENGINE PARAMETERS | | |
| Rated Engine Speed (RPM) | | 1,800 |
| Rated Engine Speed (RPM) | | 1,800 |
| POWER ADJUSTMENT FOR AMBIENT CONDITION | | |
| Temperature Deration NG & LP | 77°F before derate | 3.3% per 10°F above 77°F |
| Altitude Deration | 3% | for every 1,000 ft above 600 ft |

CONTROLLER FEATURES

| Two-Line Plain Text LCD Display | |
|---|--|
| Mode Switch: AUTO | Automatic Start on Utility failure. 7 day exerciser. |
| 0FF | Stops unit. Power is removed. Control and charger still operate. |
| | Start with starter control, unit stays on. If utility fails, transfer to load takes place. |
| Programmable Start Delay Between 10-30 Seconds | 10 sec standard |
| Engine Start Sequence | |
| Engine Warm-up | 5 sec |
| Engine Cool-Down | |
| Starter Lock-Out. | |
| Smart Battery Charger | |
| Automatic Voltage Regulation With Over and Under Voltage Protection | |
| Automatic Low Oil Pressure Shutdown | |
| Overspeed Shutdown | |
| High Temperature Shutdown | |
| Overcrank Protection | Standard |
| Safety Fused | |
| Failure to Transfer Protection | |
| Low Battery Protection | |
| 50 Event Run Log | |
| Future Set Capable Exerciser | |
| Incorrect Wiring Protection | |
| Internal Fault Protection | |
| Common External Fault Capability | |
| Governor Failure Protection | |

GENERAC

available accessories

| Model # | Product | Description |
|---|---|---|
| G007169-0 | Mobile Link [®] 4G LTE Cellular Accessory | Generac's Mobile Link allows you to check the status of your generator from anywhere that you have access to an Internet connection from a PC or with any smart device. You will even be notified when a change in the generator's status occurs via e-mail or text message. Note: Harness Adapter Kit required. Available in the U.S. only. |
| G009883-0 | Cold Weather Kit | If the temperature regularly falls below 32 $^{\circ}$ F (0 $^{\circ}$ C), install a cold weather kit to maintain optimal battery temperature. Kit consists of battery warmer with thermostat built into the wrap. |
| G009884-0 | Extreme Cold Weather Kit | Recommended where the temperature regularly falls below 32 °F (0 °C) for extended periods of time. For liquid cooled units only. |
| G005651-0 | Base Plug Kit | Add base plugs to the base of the generator to keep out debris. |
| G005703-0 - Bisque | Paint Kit | If the generator enclosure is scratched or damaged, it is important to touch-up the paint to protect from future corrosion. The paint kit includes the necessary paint to properly maintain or touch-up a generator enclosure. |
| G009882-0 | Scheduled Maintenance Kit | The Liquid-Cooled Scheduled Maintenance Kits offer all the hardware necessary to perform complete maintenance on Generac liquid-cooled generators. |
| G006510-0 | E-Stop | E-stop allows for immediate fuel shutoff and generator shutdown in the event of an emergency. |
| G007005-0 | Wi-Fi LP Fuel Level Monitor | The Wi-Fi enabled LP fuel level monitor provides constant monitoring of the connected LP fuel tank. Monitoring the LP tank's fuel level is an important step in making sure your generator is ready to run during an unexpected power failure. Status alerts are available through a free application to notify when your LP tank is in need of a refill. |
| G007000-0 (50 amp) G007006-0 (100 amp) | Smart Management Module | Smart Management Modules (SMM) are used to optimize the performance of a standby generator. They manage large electrical loads upon startup and shed them to aid in recovery when overloaded. In many cases, using SMM's can reduce the overall size and cost of the system. |
| G009885-0 | 400 A CB Kit | $400\ A$ Circuit Breaker Kit designed for three phase products built with a factory installed circuit breaker greater than $400\ A.$ |
| A0000018981 | Ultrasonic Cleaner Solution | An ultra-concentrated anti-corrosive cleaning solution engineered to reach the smallest cavities to clean the toughest contaminants. This water based formula is non-toxic, biodegradable, safe for both metal and plastic surfaces, and is superior in rinsability. |
| A0000019001 | All Surface Protectant | All surface protectant for vinyl, rubber, plastics creates a barrier that seals & protects surfaces from water, UV rays while renewing the look of the surface. |

100 kW

installation layout

GENERAC

Drawing #A0001453011 (1 of 2)



SEE NOTE 11 EITHER SIDE RIGHT SIDE

ether sde ETHER SIDE ROOF TOP

SPARK PLUGS

MUFFLER FAN BELT BATTERY

1. MINIMARIA RECURRENCE IN STATE IN THE STATE IN THE STATE IN THANKING IN MINIMARIAN RECURRENCE IN STATE OF UNDER SERVICING THE SUBPLIES WITH UNIT FOR CONCRETE PAD GUIDELINES.

ALLOW SUFFICIENT ROOM VIA LISDES OF THE GENERATOR FOR MAINTENANCE AND SERVICING THIS UNIT MUST BE INSTALLED IN ACCRODANCE WITH CURRENT APPLICABLE INFRA 77 AND NFF 70 STANDARDS AS WELL AS ANY OTHER FEDERAL, STATE. AND LOCAL CODES.

3. CONTROC PARIEL OF CHOIL PREMAINAL ON REAR OF GENERATOR.

4. INSIGH STRUEUP AREA FOR ACL LOAD LEAD CONDUIT CONNECTION, NEUTRAL CONNECTION, SETTING STRUEUP AREA FOR ACL LOAD LEAD CONDUIT CONNECTION, NEUTRAL CONNECTION, BATTERY CHARGER ROO VIOUR FOR ACCESS.

4. INSIGH OF GRAVITY AND WIRES HEAN COVER FOR ACCESS.

5. CENTER OF GRAVITY AND WIGHT MAY CHANGE DUE TO UNIT OPTIONS.

6. BOTTOM OF GENERATOR SET MUST BE ENCLOSED TO PREVENT PEST INTRUSION AND RECRECULATION OF DISCHARGE ARE ANDOR IMPROPER COOLING AIR FLOW.

7. REFERENCE OWNERS MINAUAL. FOR LITTING WARNINGS.

8. MOUNTING BOLTS OR STUDGS TO MOUNTING SUFFACE SHALL BE 5/8-11 GRADE 5 (USE STANDARD SEE FLOW OF INTAKE ARE DISCHARGE AIR AND CHANGES.

9. MIST ALLOW FREE FLOW OF INTAKE AND MAXIMUM RESTRICTION REQUIREMENTS.

10. GENERATOR MUST BE INTAKE ARE DISCHARGE AIR AND EXHAURTED.

11. REMOVE FRONT END PARIE TO ACCESS EXHAUST MIFFLER. ACCESS AVAILABLE THROUGH DOORS TO FAN BELT.

REFERENCE OWNERS MANUAL FOR PERIODIC REPLACEMENT PART LISTINGS.

RIGHT VIEW 2267 [89.3] TYP LOCKING VICE ACTION LATCH, ONE PER DOOR TWO LIFT OFF DOORS PER SIDE OF GENERATOR ϕ 63.5 |2.50] $^\perp$ Lifting eye (4X) [23] TYP 28 1761 [69.3] Overall Height CUSTOMER ACCESS
ASSEMBLY, CONTROL
PANEL ACCESS
BATTERY CHARGER
LOCATED WITHIN
SEE NOTE 3 & 4

| | | ATA | ⊑ | ļ |
|-------------------------------|--------------------------|-------------|-----------------------------------|---|
| → 1003 [39.5] → | OVERALL WID IN | WEIGHT DATA | WEIGHT GENSET ONLY KG [LBS] | |
| 1003 | OVERAL | | ENCLOSURE MATERIAL | |
| REAKER 3 | | | ENGINE/KW | |
| CIRCUIT BREAKER SEE NOTE 3 | CONNECTION FEMALE TEE | ASE TRAME | | |

▲ 47 [1.8] TYP

| ENGINE/KW | ENCLOSURE MATERIAL | WEIGHT GENSET ONLY KG [LBS] | Weight Weight Genset Only Shipping Skid Kg (LBS) KG (LBS) | SHIPPING WEIGHT KG [LBS] |
|------------|-----------------------|-----------------------------------|---|-----------------------------|
| 9.0L/100KW | AL | 1292 [2848] | 79 [175] | 1371 [3024] |
| | | | | |

COOLANT RECOVERY BOTTLE RADIATOR DRAIN HOSE AIR CLEANER ELEMENT RADIATOR FILL CAP വ —— 1228 —— 148.4] C.O.G. (SEE NOTE E Battery 12v— GRP 31F NEGATIVE GROUND P/N GO6ff19

OIL DRAIN HOSE

DRAIN EXHAUST MUFFLER— ENCLOSED WITHIN GENERATOR ENCLOSURE SEE NOTES 9, 10 & 11

REMOVE COVER FOR-ACCESS TO RADIATOR FILL CAP

TOP VIEW 850 [33.5] H DOOR WIDTH TYP RADIATOR/EXHAUST DISCHARGE AIR

AIR INTAKE

LEFT VIEW RADIATOR DRAIN

FUEL LINE CO 1-174" NPT FE THROUGH BAS

DIMENSIONS: MM [INCH]

7 of 7



